Product datasheet

Specifications





Acti9 Isobar P B - distribution board - 12 ways TP+N

Local distributor code: 405639335

SEA9BPN12

EAN Code: 5018934007687

Main

Range	Acti9	
Product Name	Acti9 Isobar P B	
Product Or Component Type	t Type Distribution board	
Device Application	Distribution	
Enclosure Type	Standard	
Provided Equipment	Earth stud	
	Enclosure	
	Door	
	Front cover	
	Pan assembly	
	Neutral terminal block	
	Earth terminal block	
	Blanking plate	
	Removable gland plates	
Colour	Cream (RAL 9001)	

Complementary

· · · · · · · · · · · · · · · · · ·	
Enclosure Mounting	Surface
Poles Description	3P + N
[le] Rated Operational Current	250 A at 400/415 V AC 250 A at 230/240 V AC
Breaking Capacity	25 kA
Overvoltage Category	IV
[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	6 kV
Incomer Device Options	Switch disconnector - 3P + N Switch disconnector - 4P MCCB - 4P Terminal block - 4P Contactor - 4P RCCB - 4P
Protection Device Options At Outgoer	Miniature circuit breaker (MCB) 63 A Residual current circuit breaker with overcurrent protection (RCBO) 45 A 100 mA Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A 100 mA
Number Of Ways	12 ways (3P) outgoer
Enclosure Material	Steel
Surface Treatment	Ероху
Surface Finish	Powder paint

Height	700 mm
Width	470 mm
Depth	139 mm
Net Weight	13.5 kg

Environment

Standards	BS EN 61439-3
Ip Degree Of Protection	IP2X without cover internal conforming to BS EN 60529 IP3x with cover external conforming to BS EN 60529
Ik Degree Of Protection	IK05
Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4080 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.500 cm
Package 1 Width	48.500 cm
Package 1 Length	70.500 cm
Package 1 Weight	14.828 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	18
Package 2 Height	112.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	291.080 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information	Yes
Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations