

Product datasheet

Specifications



Acti9 Isobar B P - split metered distribution board - 125A - 14 + 8 ways TP+N

SEA9BPN12514S8

EAN Code: 5018934007694

Main

Range	Acti9
Product Name	Acti9 Isobar P B
Product Or Component Type	Distribution board
Device Application	Distribution
Enclosure Type	Split meter
Door Type	Overall
Provided Equipment	enclosure door front cover pan assembly neutral terminal block earth terminal block earth stud blanking plate removable gland plates switch disconnecter 4P 125 A incomer
Colour	Cream (RAL 9001)

Complementary

Enclosure Mounting	Surface
Poles Description	3P + N
[Ie] Rated Operational Current	125 A at 220/240 V AC 125 A at 400/415 V AC
Breaking Capacity	25 kA
Overvoltage Category	IV
[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	6 kV
Incomer Device Options	Switch disconnecter - 3P + N Switch disconnecter - 4P MCCB - 4P Terminal block - 4P RCCB - 4P
Protection Device Options At Outgoer	Miniature circuit breaker (MCB) 63 A Residual current circuit breaker with overcurrent protection (RCBO) 45 A 100 mA Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A 100 mA
Number Of Ways	14 ways (3P)outgoer for lower pan assembly 8 ways (3P)outgoer for upper pan assembly
Enclosure Material	Steel
Surface Treatment	Epoxy

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Surface Finish	Powder paint
Height	1290 mm
Width	470 mm
Depth	139 mm
Net Weight	16 kg

Environment

Standards	BS EN 61439-3
Ip Degree Of Protection	IP3x external conforming to BS EN 60529 IP20 internal conforming to BS EN 60529
Ik Degree Of Protection	IK05
Pollution Degree	3
Ambient Air Temperature For Operation	-35...70 °C
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.500 cm
Package 1 Width	51.300 cm
Package 1 Length	133.000 cm
Package 1 Weight	29.000 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	90.000 cm
Package 2 Width	107.000 cm
Package 2 Length	150.000 cm
Package 2 Weight	302.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information

Yes

 Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations