Product datasheet

Specifications





Acti9 Isobar P B - panel fixing pan assembly - 12 ways TP+N

Local distributor code: 405639393

SEA9BPN12TN

EAN Code: 3606489484644

Main

Range	Acti9
Product Or Component Type	Pan assembly
Device Application	Distribution

Complementary

[In] Rated Current	250 A
Incomer Device Options	Switch disconnector - 3P Terminal block - 3P MCCB - 3P
Protection Device Options At Outgoer	Miniature circuit breaker (MCB) 63 A max Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A max
[Icw] Rated Short-Time Withstand Current	16 kA
Number Of Ways	12 ways - 3P + N
Height	346 mm
Width	375 mm
Depth	94 mm
Length	324 mm
Busbar Pitch	18 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	30.5 cm
Package 1 Length	39.0 cm
Package 1 Weight	5.722 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information	Yes
Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations