



Acti9 Isobar P B - pan assembly - 18 ways TP + earth + neutral

Local distributor code:

405639513 SEA9BPN18PEV

EAN Code: 3606489484699

Main

Range	Acti9
Product Or Component Type	Pan assembly
Device Application	Distribution

Complementary

oompromontar y	
[In] Rated Current	250 A
Incomer Device Options	Switch disconnector - 4P
	Terminal block - 4P
	RCCB - 3P + N
	MCCB - 3P + N
	Contactor - 4P
Protection Device Options At	Miniature circuit breaker (MCB) 63 A max
Outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max
	Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A max
Number Of Ways	1 way (incomer) - 3P + N + E
	18 ways (outgoer)
Short-Circuit Withstand	16 kA
Number Of Poles	54 x 18 mm
Height	746 mm
Width	375 mm
Depth	105 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	39.0 cm
Package 1 Length	76.0 cm
Package 1 Weight	7.625 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information



Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations