



Acti9 Isobar B dual source 125 A - 4 pole incomer

Local distributor code: 405638572

SEA9PNDSI

EAN Code: 3606489555153

Main

Range	Acti9
Product Or Component Type	Dual source incomer
Device Application	Distribution
Provided Equipment	Extension box
Colour Tint	White
Colour Code	RAL 9001

Complementary

[le] Rated Operational Current	125 A at 415 V AC
Poles Description	4P
Mounting Mode	Surface mounting
Enclosure Material	Steel
Enclosure Height	270 mm
Width	475 mm
Depth	140 mm
Internal Depth	102 mm

Environment

Ip Degree Of Protection IP3x

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	34.0 cm
Package 1 Length	49.0 cm
Package 1 Weight	7.765 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information



Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations