

# Product datasheet

Specifications



## discrete I/O connecting cable - 2 m - for modular base controller

ABFT20E200

### Main

|                                       |  |
|---------------------------------------|--|
| Accessory / Separate Part Category    | Connection accessories                               |
| Accessory / Separate Part Type        | Connecting cable                                     |
| Accessory / Separate Part Designation | Discrete I/O connecting cable                        |
| Product Compatibility                 | TWDDDO16TK<br>TWDDDI16DK<br>TWDDDI32DK<br>TWDDDO32TK |
| Accessory / Separate Part Destination | Modular base controller                              |
| Range Compatibility                   | Advantys Telefast ABE7<br>Twido                      |

### Complementary

|                       |   |
|-----------------------|---|
| Cable Length          | 2 m   |
| Cable Cross Section   | 0.08 mm²  |
| Electrical Connection | 1 connector HE10, 20 ways for controller side<br>1 connector HE10, 20 ways for Telefast ABE7 side |
| Awg Gauge             | AWG 28  |
| Width                 | 165 mm  |
| Height                | 20 mm   |
| Depth                 | 180 mm  |
| Net Weight            | 0.14 kg   |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 2.0 cm  |
| Package 1 Width              | 16.5 cm |
| Package 1 Length             | 18.0 cm |
| Package 1 Weight             | 169.0 g |
| Unit Type Of Package 2       | S02     |
| Number Of Units In Package 2 | 20      |
| Package 2 Height             | 15.0 cm |
| Package 2 Width              | 30.0 cm |
| Package 2 Length             | 40.0 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |          |
|------------------|----------|
| Package 2 Weight | 3.732 kg |
|------------------|----------|

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|                       |   |     |
|-----------------------|---|-----|
| ✓                     | Reach Free Of Svhc  |     |
| ✓                     | Toxic Heavy Metal Free  |     |
| ✓                     | Mercury Free  |     |
| ✓                     | Rohs Exemption Information  | Yes |
| Reach Regulation      | REACH Declaration   |     |
| Eu Rohs Directive     | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration   |     |
| China Rohs Regulation | China RoHS declaration  |     |
| Weee                  | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |     |