# **Product datasheet**

Specifications



## ARGUS Presence Dual-Tech - 1ch

CCT551011

#### Main

Range Of Product	ARGUS standard movement detector
Range	ARGUS
Product Or Component Type	Presence detector with IR receiver
Load Type	LED lighting: : 100 W Incandescent lamps: : 2000 W - 230 V Halogen lamp: : 1000 W - 230 V Halogen lamp with standard electronic transformer: 1000 VA Halogen lamp with standard ferromagnetic transformer: 1000 VA Fluorescent tube: 900 VA, 100 μF
Colour Tint	White

#### Complementary

Network Frequency	50/60 Hz
Input Function	Switch External trigger
Output Voltage	220250 V
Output Current	10 A
Number Of Channels	2
Control Type	Movement sensor
Function Available	Switching, toggling, dimming
Light Intensity Adjustment	101000 lux
Horizontal Detection Angle	360 °
Mounting Height	2.5 m

#### Environment

Ip Degree Of Protection

IP20

## Packing Units

I acking Onits	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.2 cm
Package 1 Width	11.7 cm
Package 1 Length	17.7 cm
Package 1 Weight	462 g
Unit Type Of Package 2	CAR

Number Of Units In Package 2	8
Package 2 Height	40 cm
Package 2 Width	31 cm
Package 2 Length	50 cm
Package 2 Weight	10.29 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	160
Package 3 Height	95 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	88.92 kg

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information