

Product datasheet

Specifications



NFC cartridge fuses, TeSys GS, cylindrical 10mm x 38mm, fuse type gG, 500VAC, 4A, without striker

DF2CN04

Main

Range Of Product	TeSys fuse-disconnector
Product Or Component Type	Cartridge fuse
Device Short Name	DF2
[Ue] Rated Operational Voltage	500 V AC
[In] Rated Current	4 A 500 V
Fuse Size	10 x 38 mm
Fuse Type	NFC
Quantity Per Set	Set of 10

Complementary

Fuse Curve	GG
Net Weight	0.01 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.1 cm
Package 1 Width	1.1 cm
Package 1 Length	3.7 cm
Package 1 Weight	6 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.3 cm
Package 2 Width	5.5 cm
Package 2 Length	8 cm
Package 2 Weight	77 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	480
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Weight	3.879 kg
------------------	----------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div><div>✓</div><div>Reach Free Of Svhc</div></div>	
<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
<div><div>✓</div><div>Pvc Free</div></div>	
<div>Reach Regulation</div>	<div>REACH Declaration</div>
<div>Eu Rohs Directive</div>	<div><div>Compliant</div><div>EU RoHS Declaration</div></div>
<div>China Rohs Regulation</div>	<div><div>China RoHS declaration</div><div>Pro-active China RoHS declaration (out of China RoHS legal scope)</div></div>
<div>Weee</div>	<div>The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins</div>