

Product datasheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, Orange, 4mm², long size, 10 sets of 100

DZ5CE043

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Long
Standards	NF C 63-023
Type Of Packing	String of bags
Quantity Per Set	10 sets of 100
Cable Cross Section	4 mm ²

Complementary

Cable End Type	Single conductor
Additional Information	Without marker tag holder
Colour	Orange
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 12
Bezel Size	Ø 5.4 mm
Tube Diameter	3.2 mm
Length	26 mm
Tube Length	18 mm
Net Weight	0.455 kg

Environment

Product Certifications	UL
Ambient Air Temperature For Operation	-20...105 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm

Package 1 Weight	0.400 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	5.500 cm
Package 2 Width	12.000 cm
Package 2 Length	25.000 cm
Package 2 Weight	411.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	5000
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.257 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
