Product datasheet

Specification





Cable end, Linergy TR cable ends, Single conductor, red, 1mm², medium size, markable, 10 sets of 100

DZ5CA010

Main

Range Of Product	Linergy	
Product Or Component Type	Cable end	
Cable End Size	Medium	
Standards	NF C 63-023	
Type Of Packing	String of bags	
Quantity Per Set	10 sets of 100	
Cable Cross Section	1 mm²	

Complementary

Cable End Type	Single conductor
Additional Information	With integrated marker tag holder
Colour	Red
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 18
Bezel Size	Ø 3.5 mm
Tube Diameter	1.7 mm
Length	14 mm
Tube Length	8 mm
Cad Overall Depth	32 mm
Net Weight	0.16 kg

Environment

Product Certifications	UL
Ambient Air Temperature For Operation	-20105 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm

Package 1 Length	1.400 cm
Package 1 Weight	0.100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	4.000 cm
Package 2 Width	11.000 cm
Package 2 Length	21.000 cm
Package 2 Weight	164.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	70000
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	12.412 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
Ø	Toxic Heavy Metal Free
Ø	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free
②	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations