# **Product datasheet**

Specifications

Green Premium<sup>™</sup>



10A 2 Pin Switched Socket Outletv

E3015US\_WW

() Discontinued on: 30 Jun 2023

Main

Range	Neo C-Metro	
Product Or Component Type	Power socket-outlet	
Switch Function	1-pole	
Outlet Poles Configuration	2P with shutters	
Outlet Standard	GB 16915.1 GB 2099.1	
Colour Tint	White	

#### Complementary

Wiring Device Mounting	Flush
	Surface
Rated Current	10 A at 250 V AC 50/60 Hz
Material	Brass: metal parts
	Nylon: shutter
	Polycarbonate: plastic part
	Steel: metal parts
Load Type	Resistive
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Depth	20 mm

#### Environment

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use
Standards	GB 16915.1

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	8.7 cm

Package 1 Length	8.7 cm
Package 1 Weight	77 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	630 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	7300 g

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations