


Product datasheet

Specifications



Auxiliary contact, TeSys GS, 1 C/
O, 3P, 160A, fuse type DIN, size 0,
for GS1 GS2 Blown fuse

GS1AF33

Main

Range Of Product	TeSys
Device Short Name	GS1AF
Product Or Component Type	Auxiliary contact
Contact Application	Blown fuse signalling
Contacts Type And Composition	1 C/O
Contact Operation	Instantaneous
[Ith] Conventional Free Air Thermal Current	16 A (at 40 °C)
[Ie] Rated Operational Current	12 A at 24 V DC-13 2 A at 48 V DC-13 3 A at 400 V AC-15 4 A at 230 V AC-15 0.4 A at 220 V DC-13 0.6 A at 110 V DC-13

Complementary

Range Compatibility	TeSys TeSys GS fuse-switch disconnecter
Mechanical Durability	30000 cycles
Electrical Durability	30000 cycles AC-15
Product Compatibility	GS
Poles Description	3P
Switch Rated Current	160 A
Fuse Type	NFC DIN
Fuse Size	0
Net Weight	0.036 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	9.5 cm
Package 1 Length	15.1 cm
Package 1 Weight	36 g
Unit Type Of Package 2	S01

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	20
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	896 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information