

# Product datasheet

Specifications



Cam switch Operating head,  
Harmony K, for multifixing, plastic,  
yellow, 45 x 45 mm, red handle,  
marked 0-1, 90°, padlocking

KCG3Y

## Main

Range Of Product	Harmony Series K
Product Or Component Type	Cam switch operating head
Component Name	KCG
Product Compatibility	Front mounting bodies 12 and 20 A by multifixing
Cam Switch Head Type	With front plate 45 x 45 mm
Type Of Operator	Red handle, length = 35 mm
Rotary Handle Padlocking	With
Presentation Of Legend	With yellow legend, 0 - 1
Switching Angle	90 °

## Complementary

Mechanical Durability	1000000 cycles
Cad Overall Width	45 mm
Cad Overall Height	45 mm
Cad Overall Depth	45 mm
Length	35 mm
Net Weight	0.024 kg

## Environment

Protective Treatment	TC
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-40...70 °C
Shock Resistance	30 gn conforming to IEC 68-2-27
Vibration Resistance	5 gn conforming to IEC 68-2-6 (f = 10...150 Hz)
Ip Degree Of Protection	IP40 conforming to IEC 529 IP40 conforming to NF C 20-010

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	7.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	7.0 cm
Package 1 Weight	24.0 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	