



## 35mm symetrical DIN rail -L 380mm for using with NSYTCSxx in PLM54 and 64

NSYCS400PLM

### Main

Anwendung	Multi-purpose	
Range	Spacial	
Product Or Component Type	Rail	
Accessory / Separate Part Category	Mounting accessory	
Type Of Rail	Symmetrical DIN	
Enclosure Nominal Dimensions	-	
Mounting Support	Plastic nut	
Range Compatibility	Thalassa Thalassa PLM	
Device Composition	1 rail	
Quantity Per Set	Set of 2	

## Complementary

Material	Steel	
Surface Finish	Zinc coated	
Fixing Mode	By fixing element - rear of enclosure location	
Adjustment	DIN rail adjustment in height, pitch 25 mm	
Length	410 mm	
Height	35 mm	
Width	7.2 mm	
Thickness	1 mm	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.000 cm
Package 1 Width	35.000 cm
Package 1 Length	41.000 cm
Package 1 Weight	142.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	2.000 cm

Package 2 Width	35.500 cm
Package 2 Length	41.500 cm
Package 2 Weight	286.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	36
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	5.798 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations