Product datasheet

Specifications





Spacial CRN plain door w/o mount.plate. H800xW600xD200 IP66 IK10 RAL7035..

NSYCRN86200

Main

| Range | Spacial |
|-----------------------------|---|
| Product Name | Spacial CRN |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure Nominal Height | 800 mm |
| Enclosure Nominal Width | 600 mm |
| Enclosure Nominal Depth | 200 mm |
| Installation Accessory Type | Wall-mounting |
| Device Composition | 1 body 1 cable gland plate 1 door 1 lock |
| Door Type | Plain |
| Mounting Plate Description | Without mounting plate |

Complementary

| · · · · · · · · · · · · · · · · · · · | |
|---------------------------------------|--|
| Body Type | Back welded with double profile forming a protected sealed area Sides made from a single folded section |
| Number Of Doors | Front face: 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 3 mm double-bar lock |
| Type Of Gland Plate | Standard |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges Cable gland plate by screws |
| Material | Body: steel |
| Surface Finish | Epoxy-polyester powder |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | cUL UL DNV-GL |
| Net Weight | 18.138 kg |

Environment

| Ip Degree Of Protection | IP66 conforming to IEC 60529 |
|-------------------------|------------------------------|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 21.500 cm |
| Package 1 Width | 61.500 cm |
| Package 1 Length | 81.500 cm |
| Package 1 Weight | 18.344 kg |
| Unit Type Of Package 2 | РАМ |
| Number Of Units In Package 2 | 15 |
| Package 2 Height | 197.000 cm |
| Package 2 Width | 100.000 cm |
| Package 2 Length | 120.000 cm |
| Package 2 Weight | 288.160 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |