



# 4 wall fixing brackets in stainless steel AISI 304 for Spacial S3X



NSYPFCX

#### Main

Range	Spacial	
Accessory / Separate Part Category	Fixing accessory	
Product Or Component Type	Wall fixing support	
Device Application	Multi-purpose	
<b>Enclosure Nominal Dimensions</b>	is -	
Mounting Location	Rear of enclosure	
Installation Accessory Type	Accessory Type Horizontal or vertical position	
Range Compatibility	Spacial Spacial CRN Spacial Spacial S3X	
Device Composition	fixing screws 4 lug 4 pre-mounted sealing gasket	
Quantity Per Set	Set of 1	

### Complementary

Material	Stainless steel 304	
Fixing Mode	Screwed - screw type M8 Screwed - screw type M6	
Permanent Permissible Load	250 kg 249.93 kg	
Height	Real: 74 mm	
Width	Real: 42 mm	
Depth	Wall-enclosure separation : 12 mm Wall-enclosure separation : 11.94 mm	
Net Weight	0.3 kg	

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	8.0 cm
Package 1 Length	15.5 cm
Package 1 Weight	292.0 g
Unit Type Of Package 2	CAR

Number Of Units In Package 2	40
Package 2 Height	26.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	12.05 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	480
Package 3 Height	100.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	158.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations