# **Product datasheet**

Specifications





## SPACIAL S3X stainless 304L, Scotch Brite® finish, H700xW500xD250 mm.

NSYS3X7525

#### Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	700 mm
Nominal Width	500 mm
Nominal Depth	250 mm
Product Installation	Wall-mounting
Device Composition	1 body 1 door 2 lock: door 2 perforated vertical profile drilled: door

### Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Plain
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	2 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface Finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net Weight	17.36 kg

### Environment

Standards	IEC 62208
Product Certifications	CAN/CSA 22 UL 508 type A

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Specific hygiene Corrosive

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27.0 cm
Package 1 Width	51.5 cm
Package 1 Length	72.0 cm
Package 1 Weight	17.36 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	21
Package 2 Height	208.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	384.0 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance



Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations