



# Metallic mounting plate for PLA enclosure H1500xW1250mm

NSYPMM1512

### Main

Range	Thalassa	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	-	
Mounting Location	Back inserts Step slide	
Mounting Plate Description	Plain	
Range Compatibility	Thalassa Thalassa PLA Thalassa Thalassa PHD	
Device Composition	tion 1 mounting plate	
Material	Galvanised steel	

## Complementary

Fixing Mode	By screws - screw type M8 - on back inserts location	
Permanent Permissible Load	150 kg	
Height	Nominal: 1500 mm Real: 1390 mm	
Width	Nominal: 1250 mm Real: 1125 mm	
Depth	Real : 125 mm	
Thickness	2.5 mm	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	112.000 cm
Package 1 Length	137.500 cm
Package 1 Weight	30.000 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	25
Package 2 Height	45.000 cm

Package 2 Width	200.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	782 343 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations