

# Product datasheet

Specifications



## NSYTR end cover for screw single-level terminal block 1x1 - 2.5 to 10mm²

NSYTRAC22

### Main

Range	Lineryg
Product Name	Lineryg TR
Product Or Component Type	Cover plate
Device Short Name	TRA
Accessory / Separate Part Category	Insulation accessory
Product Compatibility	TRV screw terminal - passthrough terminal block, length = 47.7 mm TRV screw terminal - protective earth terminal block, length = 47.7 mm TRV screw terminal - blade disconnect terminal block, length = 55 mm
Thickness	2.2 mm

### Complementary

Cable Cross Section	6 mm² 2.5 mm² 4 mm² 10 mm²
Number Of Connections	2
Number Of Measurement Input	2 1
Quantity Per Set	Set of 50
Net Weight	2.4 g
Colour	Grey

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	4.000 cm
Package 1 Length	4.700 cm
Package 1 Weight	2.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	3.000 cm
Package 2 Width	13.000 cm
Package 2 Length	17.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	127.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	3600
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	9.950 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)