

Product datasheet

Specifications



booted head for pushbutton XAC-B -
green - 4 mm, -25..+70 °C

XACB9113

Main

Range Of Product	Harmony XAC
Product Or Component Type	Head for push-button
Component Name	XACB
Marking	Unmarked
Operator Additional Information	Booted
Operating Travel	4 mm
Cap/Operator Or Lens Colour	Green
Product Compatibility	XENC.... XEND.... XESB2011 XESD2241 XENB.... XESD2251 XESD2201
Sale Per Indivisible Quantity	10

Complementary

Net Weight	0.005 kg
------------	----------

Environment

Standards	IEC 60947-5-1 CSA C22.2 No 14 EN 60947-5-1
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	100 gn conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	10.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	12.0 cm
Package 1 Weight	6.0 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	3.0 cm
Package 2 Width	12.0 cm
Package 2 Length	10.0 cm
Package 2 Weight	63.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	851.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration