# **Product datasheet**





# Prewired rotating mirror beacon, Harmony XVR, 106mm, orange, without buzzer, 24V AC/DC

XVR10B05

### Main

Range Of Product	Harmony XVR	
Product Or Component Type	Prewired rotating mirror beacon	
Sound Signalling	Without	
Device Short Name	XVR	
Mounting Diameter	106 mm	
Ip Degree Of Protection	IP55 (with accessory) conforming to IEC 60529 IP23 conforming to IEC 60529	
[Us] Rated Supply Voltage	24 V AC/DC	
Light Source	High luminosity LED, orange	

# Complementary

Material	ABS (acrylonitrile butadiene-styrene): body part PMMA (polymethyl methacrylate): globe
Cad Overall Width	106 mm
Cad Overall Depth	106 mm
Net Weight	0.5 kg
Marking	CE
Product Mounting	By 3 M4 screws
Supply Voltage Limits	1930 V DC 21.626.4 V AC
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	125 mA
Flashing Frequency	2.3 Hz
Clamping Connection Capacity	0.83 mm²
Awg Gauge	AWG 18
Cable Length	400 mm

#### **Environment**

Standards	IEC 61000-6-2 IEC 61000-6-4
Product Certifications	UL
Protective Treatment	TC
Ambient Air Temperature For Storage	-3570 °C

Ambient Air Temperature For Operation	-1050 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	14.0 cm
Package 1 Length	19.5 cm
Package 1 Weight	624.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	6.372 kg

# **Contractual warranty**

Warranty 18 months



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance



Rohs Exemption Information

#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


### XVR10B05

### **Dimensions Drawings**

## Rotating Mirror Beacon

#### **Dimensions**





# **Product datasheet**

### XVR10B05

Mounting and Clearance

## Rotating Mirror Beacon

#### **Panel Cut-out**

