# **Product datasheet**

Specifications





# Powerpact 4 - panelboard - 800A - 12 ways - 3P - Style E

Local distributor code:

387299110 MG8C12

EAN Code: 3606485858838

#### Main

Range	PowerPact	
Product Or Component Type	Panelboard	
Product Name	PowerPacT 4	
Device Application	Distribution	
Colour	Cream (RAL 9001)	
Provided Equipment	removable bottom gland plate	

### Complementary

[In] Rated Current	800 A	
Number Of Ways	12 ways (3P) 36 ways (1P)	
[Ue] Rated Operational Voltage	415 V 50 Hz AC	
Breaking Capacity	50 kA AC 1 s	
Enclosure Material	epoxy-polyester powder steel	
Thickness	Cover: 1.2 mm Enclosure: 1.6 mm	
Cable Entry	Bottom entry at main	
Device Mounting	Wall mounted	
Height	1896 mm	
Width	850 mm	
Depth	260 mm	
Horizontal Fixing Centres	172 mm	
Vertical Fixing Centres	1306 mm	

#### **Environment**

Ip Degree Of Protection	IP3x	
Standards	BS EN 61439-1	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	126 cm

Package 1 Width	189 cm	
Package 1 Length	89 cm	
Package 1 Weight	105 kg	

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations