

Product datasheet

Specifications



Powerpact 4 - Molded Case Circuit Breaker - 1P - 63A - 230 V - L2

Local distributor code:

386962273

MGP0631L2

 **Discontinued on:** 20 Mar 2023

EAN Code: 3606486440216

 **Discontinued**

Main

Range Of Product	PowerPacT 4
Product Or Component Type	Circuit breaker
Device Application	Distribution
Poles Description	1P
[In] Rated Current	63 A at 40 °C
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Suitability For Isolation	Yes conforming to BS EN 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	25 kA Icu at 230 V AC 50/60 Hz
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Protection Functions	LI
Control Type	Toggle
Circuit Breaker Mounting Mode	Panel-mounted

Complementary

[Ui] Rated Insulation Voltage	750 V
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ics] Rated Service Short-Circuit Breaking Capacity	25 kA at 230 V AC 50/60 Hz
Mechanical Durability	20000 cycles
Electrical Durability	20000 cycles at 277 V In/2 10000 cycles at 277 V In
Mounting Support	Backplate
Mounting Position	Horizontal and vertical
Phase Connection	L2
Number Of Modules	1 module(s)35 mm
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)
Trip Unit Rating	63 A at 40 °C
Thermal Protection Adjustment Range	63 A
Earth-Leakage Protection	Without

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	BS EN 60947-2
-----------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins