


Product datasheet

Specifications



Acti9 IsoBar P B - pan assembly - 24 ways TP + earth + neutral

Local distributor code:

405639555

SEA9BPN24E

EAN Code: 5018934007885

Main

Range	Acti9
Product Or Component Type	Pan assembly
Device Application	Distribution

Complementary

[In] Rated Current	250 A
Incomer Device Options	Switch disconnector - 4P Terminal block - 4P RCCB - 3P + N MCCB - 3P + N Contactor - 4P
Protection Device Options At Outgoer	Miniature circuit breaker (MCB) 63 A max Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A max
Number Of Ways	24 ways - 3P + N + E
Short-Circuit Withstand	16 kA
Height	896 mm
Width	375 mm
Depth	105 mm
Length	896 mm
Busbar Pitch	18 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.7 cm
Package 1 Width	41.1 cm
Package 1 Length	92.6 cm
Package 1 Weight	10.362 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	27
Package 2 Height	112.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	299.774 kg
------------------	------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information

Yes

 Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations