


# Product datasheet

Specifications



## Acti9 IsoBar P B - pan assembly - 8 ways TP + earth + neutral

Local distributor code:  
405639267

SEA9BPN8E

EAN Code: 5018934008066

### Main

Range	Acti9
Product Or Component Type	Pan assembly
Device Application	Distribution

### Complementary

[In] Rated Current	250 A
Incomer Device Options	Switch disconnector - 4P Terminal block - 4P RCCB - 3P + N MCCB - 3P + N Contactor - 4P
Protection Device Options At Outgoer	Miniature circuit breaker (MCB) 63 A max Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Residual current circuit breaker with overcurrent protection (RCBO PoN) 45 A max
Number Of Ways	8 ways - 3P + N + E
Short-Circuit Withstand	16 kA
Height	471 mm
Width	375 mm
Depth	105 mm
Length	471 mm
Busbar Pitch	18 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.000 cm
Package 1 Width	41.500 cm
Package 1 Length	50.000 cm
Package 1 Weight	5.032 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	42
Package 2 Height	115.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	223.340 kg
------------------	------------

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Rohs Exemption Information

Yes

 Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations