

Product data sheet

Specifications



Airing grille cut-out diameter 33mm IP45

NSYCAG33LP

Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	Thalassa Thalassa PLS Thalassa Thalassa PLM Thalassa Thalassa TBS
Product Or Component Type	Plastic ventilation louvre
Accessory / Separate Part Category	Thermal management accessory
Accessory / Separate Part Destination	ClimaSys ventilation system
Mounting Position	Vertical
Fixing Mode	By screws
Device Composition	2 plastic louvre

Complementary

Material	Polyamide 6
Colour	Grey (RAL 7035)
Cut-Out Dimensions	33 mm
Height	69 mm external:
Width	47 mm external:
Depth	22.5 mm external:
Ip Degree Of Protection	IP44

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	4.500 cm
Package 1 Length	7.000 cm
Package 1 Weight	26.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	4.000 cm
Package 2 Width	4.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	7.000 cm
Package 2 Weight	57.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	500
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	14.950 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations