

Product data sheet

Specifications



Outlet grille - plastic - cut out
291x291mm - ext. dim 336x316mm
- IP54

NSYCAG291LPF

Overview

Lead Time	Usually Ships within 4 Weeks
-----------	------------------------------

Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	Prisma Prisma P Prisma Prisma G
Product Or Component Type	Outlet grille
Accessory / Separate Part Category	Thermal management accessory
Accessory / Separate Part Destination	ClimaSys ventilation system
Fixing Mode	By screws Clipped
Device Composition	1 support frame 1 external part 1 G2 M1 synthetic standard filter

Complementary

Material	Injected thermoplastic (ASA PC)
Colour	External part: grey (RAL 7035)
Cut-Out Dimensions	291 x 291 mm
Height	External: 336 mm
Width	External: 316 mm
Depth	18 mm external:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.826 cm
Package 1 Width	32.004 cm
Package 1 Length	34.29 cm
Package 1 Weight	934.4 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	6
Package 2 Height	29.718 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	39.37 cm
Package 2 Length	39.37 cm
Package 2 Weight	6.11 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	131 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	145 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations