

Product datasheet

Specifications



Acti 9 modular bell transformer iTR - 230 V 50..60 Hz - output 12..24 V - 25 VA

A9A15215

Main

Range Of Product	Acti9
Product Name	Acti9 iTR
Product Or Component Type	Transformer
Device Short Name	iTR
Transformer Type	Bell transformer

Complementary

[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Output Voltage	12/24 V: +/- 15 % on load 16/32 V: off load
Output Short-Circuit Protection	Built-in
Rated Power In Va	25 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	6
Height	89 mm
Width	54 mm
Depth	60 mm
Colour	White
Auxiliary Connection Terminal	Tunnel type terminalsrigid 2.5 mm² Tunnel type terminalsflexible 2.5 mm² Tunnel type terminalsflexible with ferrule 2.5 mm²
Wire Stripping Length	6 mm
Tightening Torque	0.5 N.m

Environment

Standards	EN 60742 EN 61558-2-6 IEC 61558-2-6
Product Certifications	NF
Ip Degree Of Protection	IP20 conforming to IEC 60529
Overvoltage Category	Class II with terminal shields in option
Ambient Air Temperature For Operation	-20...55 °C
Ambient Air Temperature For Storage	-25...80 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	6.000 cm
Package 1 Length	9.500 cm
Package 1 Weight	662.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	14
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.588 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins