# **Product datasheet**

Specifications





# PratiKa industrial plug - 32 A - 3P + E - 100...130 V AC - IP67

83564

() Discontinued on: 12 Jan 2023

#### ① Discontinued

#### Main

| Range                     | PratiKa      |
|---------------------------|--------------|
| Product Or Component Type | Plug         |
| Device Short Name         | PratiKa plug |
| Plug, Socket Category     | Low voltage  |
| Poles Description         | 3P + E       |
| Network Type              | AC           |
| Outlet Standard           | Industrial   |

#### Complementary

| Mounting Mode                          | Wall-mounted                           |
|--|--|
| Plug, Socket, Control Station<br>Shape | Angled                                 |
| [In] Rated Current                     | 32 A                                   |
| [Ue] Rated Operational Voltage         | 100130 V                               |
| Network Frequency                      | 50/60 Hz                               |
| Ground Lug Clockwise Position          | 4 h                                    |
| Plug, Socket Material                  | Self-extinguishing engineering polymer |
| Contacts Material                      | Pins: nickel plated brass              |
| Connections - Terminals                | Captive screws                         |
| Cable Cross Section                    | 2.510 mm <sup>2</sup>                  |
| Cable Entry                            | Cable gland                            |
| Thread Type                            | Pg 21                                  |
| Net Weight                             | 0.502 kg                               |
| Base Dimension                         | 106 x 130 mm                           |
| Height                                 | 136 mm                                 |
| Width                                  | 106 mm                                 |
| Depth                                  | 178 mm                                 |
| Colour                                 | Grey (RAL 7035)                        |
| Voltage Colour                         | Yellow                                 |

### Environment

| Standards                                | EN 60309-1<br>EN 60309-2                        |
|--|---|
| Ip Degree Of Protection                  | IP67 conforming to IEC 60529                    |
| Ik Degree Of Protection                  | IK08 conforming to EN 62262                     |
| Fire Resistance                          | 850 °C conforming to IEC 60695-2-1              |
| Relative Humidity                        | 50 % at 40 °C<br>70 % at 30 °C<br>90 % at 20 °C |
| Operating Altitude                       | 2000 m  |
| Ambient Air Temperature For<br>Operation | 35 °C ( 86400 s )<br>-25…40 °C                  |

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Rohs Exemption Information

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration<br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |