Specifications





Regulated Power Supply, modicon power supply, 100...240V AC, 12V, 8.5A, single phase, Panel Mount

ABLP1A12085

### Main

Range Of Product	Modicon Power Supply
Product Or Component Type	Power supply
Power Supply Type	Regulated switch mode
Variant Option	Panel mount
Enclosure Material	Aluminium
Nominal Input Voltage	100240 V AC single phase
Rated Power In W	100 W
Output Voltage	12 V DC
Power Supply Output Current	8.5 A

## Complementary

oompiementai y	
Input Voltage Limits	90264 V AC
Nominal Network Frequency	5060 Hz
Network System Compatibility	TN
Maximum Leakage Current	1 mA 240 V AC
Input Protection Type	Integrated fuse (not interchangeable) 4 A
Inrush Current	45 A at 115 V
	85 A at 230 V
Power Factor	0.55 at 115 V AC
	0.45 at 230 V AC
Efficiency	88 % at 230 V AC
Output Voltage Adjustment	10.813.2 V
Power Dissipation In W	21 W
Current Consumption	< 2.3 A 115 V AC
	< 1.5 A 230 V AC
Turn-On Time	< 500 ms
Holding Time	> 20 ms 115 V AC
	> 40 ms 230 V AC
Startup With Capacitive Loads	4000 µF
Residual Ripple	< 120 mV

Meantime Between Failure [Mtbf] 700000 h at 25 °C, full load conforming to SR 332

Output Protection Type	Against overload and short-circuits, protection technology: automatic reset Against over temperature, protection technology: manual reset Against overvoltage, protection technology: manual reset		
Connections - Terminals	Screw connection: 0.752.5 mm <sup>2</sup> , (AWG 18AWG 14) without wire end ferrule Screw connection: 0.751.5 mm <sup>2</sup> , (AWG 18AWG 16) with wire end ferrule		
Line And Load Regulation	< 0.5 % at 0 to 100 % load at 25 °C < 1 % at full voltage range in line at 25 °C		
Status Led	1 LED (green) output voltage		
Depth	129 mm		
Height	30 mm		
Width	97 mm		
Net Weight	0.3 kg		
Output Coupling	Parallel Serial		
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 Double-profile DIN rail panel mounting		
Supply	SELV conforming to IEC 60950-1 SELV conforming to IEC 60204-1 SELV conforming to IEC 60364-4-41		
Dielectric Strength	3750 V AC with input to output		
Service Life	10 year(s)		
Overvoltage Category	II		

## Environment

Standards	IEC 62368-1	
	IEC 61010-1	
	EN 61010-2-201	
	EN 61204-3	
	IEC 61000-6-1	
	IEC 61000-6-2	
	IEC 61000-6-3	
	IEC 61000-6-4	
	IEC 61000-3-2	
	EN 61000-3-3	
	UL 62368-1	
	UL 61010-1	
	UL 61010-2-201	
	CSA C22.2 No 62368-1	
	CSA C22.2 No 61010-1	
	CSA C22.2 No 61010-2-201	
	EN/IEC 62368-1	
Product Certifications	CE	
	CULus	
	EAC	
	RCM	
	CB Scheme	
	KC	
Operating Altitude	5000 m	
Shock Resistance	150 m/s² for 11 ms	
Ip Degree Of Protection	IP10	
Ambient Air Temperature For Operation	-3050 °C without derating mounting position A, B, F, G < 2000 m 5070 °C with current derating of 2 % per °C mounting position A, B, F, G < 2000 m	
Electrical Shock Protection Class	Class I	
Pollution Degree	2	

Vibration Resistance	3 mm (f= 29 Hz) conforming to IEC 60068-2-6
	10 m/s <sup>2</sup> (f= 9200 Hz) conforming to IEC 60068-2-6
Electromagnetic Immunity	Immunity to electrostatic discharge - test level: 8 kV (contact discharge) conforming to IEC 61000-4-2
	Immunity to electrostatic discharge - test level: 15 kV (air discharge) conforming to IEC 61000-4-2
	Immunity to conducted RF disturbances - test level: 15 V/m (80 MHz2 GHz) conforming to IEC 61000-4-3
	Immunity to conducted RF disturbances - test level: 5 V/m (22.7 GHz) conforming to IEC 61000-4-3
	Immunity to conducted RF disturbances - test level: 5 V/m (2.76 GHz) conforming to IEC 61000-4-3
	Immunity to fast transients - test level: 4 kV (on input-output) conforming to IEC 61000-4-4
	Surge immunity test - test level: 4 kV (between power supply and earth) conforming to IEC 61000-4-5
	Surge immunity test - test level: 3 kV (between phases) conforming to IEC 61000-4-5 Immunity to conducted RF disturbances - test level: 15 V (0.1580 MHz) conforming to IEC 61000-4-6
	Immunity to magnetic fields - test level: 30 A/m (5060 Hz) conforming to IEC 61000-4-8
	Immunity to voltage dips conforming to IEC 61000-4-11 Disturbing field emission conforming to EN 55016-2-3
	Limits for harmonic current emissions conforming to IEC 61000-3-2 conforming to EN 55016-1-2 conforming to EN 55016-2-1
Electromagnetic Emission	Conducted emissions conforming to IEC 61000-6-3 Radiated emissions conforming to IEC 61000-6-4

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	14.8 cm
Package 1 Length	18.5 cm
Package 1 Weight	420.0 g
Unit Type Of Package 2	\$03
Number Of Units In Package 2	19
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	8.54 kg

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance



Rohs Exemption Information

## **Certifications & Standards**

Reach Regulation	REACh Declaration Pro-active compliance (Product out of EU RoHS legal scope)		
Eu Rohs Directive			
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		


#### **Dimensions Drawings**

#### Electrical Safety

- If the unit is use in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.
- For means of disconnection a switch or circuit breaker, located near the product, must be included in the installation. A marking as disconnecting device for the product is required.
- The device has an internal fuse. The unit is tested and approved with branch circuit protective device up to 20A. This circuit breaker can be used as disconnecting device.
- The power supply is only suitable for audio, video, information, communication, industrial and control equipment.

#### Dimensions


#### Front and Side Views



Connections and Schema


**Connections and Schema** 

#### **Correct Parallel Connection**






**Incorrect Parallel Connection** 




(1) : Load ABLx1Axxxxx-1 = ABLx1Axxxxx-2 max 2 x ABLx1Axxxxx L1 = L2  $\Delta V$  max 25 mV  $I_{Load} < 90\% 2 x I_{nom}$ 

#### **Output Voltage Balancing**



(1):  $R_{Load1}$ (2):  $R_{Load2}$  $R_{Load1} = R_{Load2}$  $I_1 = I_2 = ~ I_{nom}$ 





(1) : V<sub>out1</sub>

- (2) : V<sub>out2</sub>
- (3) : 2 x Diode,  $V_{RRM}$  > 2 x  $V_{out1/2}$ ,  $I_F$  > 2 x  $I_{nom1/2}$
- (4) : V<sub>Load</sub> = 2 x V<sub>out</sub>
- (5) : Load

#### **Connections and Schema**


	(1)		
	<40°C	<50°C	<70°C
ABLP1A12085	60°C	70ºC	90°C
ABLP1A24045	60°C	70ºC	90°C
ABLP1A24062	60ºC	70ºC	90°C
ABLP1A24100	60°C	70ºC	90°C

(1) : Ambient


Mounting and Clearance

#### Mounting


#### **Mounting Position A**




#### **Mounting Position B**




#### **Mounting Position C**




#### **Mounting Position F**



#### **Mounting Position G**




#### **Mounting Position H**



Performance Curves

#### Performance Curves


#### Mounting Position A, B and G



#### Mounting Position C and F

Y -20 -30 -10 х

#### **Mounting Position H**



X : Surrounding Air Temperature (°C)

Y: Percentage of Max Load (%)

1 : Altitude 2000 m

2 : Altitude 5000 m

Note : < 115 VAC additional derating by 0.6% / V

Life Is On Schneider