Specifications





Regulated Power Supply, modicon power supply, 100...240V AC, 24V, 6.2A, single phase, Panel Mount

ABLP1A24062

Main

Range Of Product	Modicon Power Supply
Product Or Component Type	Power supply
Power Supply Type	Regulated switch mode
Variant Option	Panel mount
Enclosure Material	Aluminium
Nominal Input Voltage	100120 V AC single phase 200240 V AC single phase
Rated Power In W	150 W
Output Voltage	24 V DC
Power Supply Output Current	6.25 A

Complementary

oompiementai y		
Input Voltage Limits	90132 V AC	
	170264 V AC	
Nominal Network Frequency	5060 Hz	
Network System Compatibility	TN	
	TT	
	IT	
Maximum Leakage Current	1 mA 240 V AC	
Input Protection Type	Integrated fuse (not interchangeable) 4 A	
Inrush Current	35 A at 115 V	
	70 A at 230 V	
Power Factor	0.55 at 115 V AC	
	0.45 at 230 V AC	
Efficiency	88.8 % at 230 V AC	
Output Voltage Adjustment	21.626.4 V	
Power Dissipation In W	29 W	
Current Consumption	< 3.2 A 115 V AC	
	< 1.9 A 230 V AC	
Turn-On Time	< 500 ms	
Holding Time	> 20 ms 115 V AC	
	> 40 ms 230 V AC	
Startup With Capacitive Loads	7000 µF	
Residual Ripple	< 170 mV	
Meantime Between Failure [Mtbf]	700000 h at 25 °C, full load conforming to SR 332	-

Output Protection Type	Against overload and short-circuits, protection technology: automatic reset Against over temperature, protection technology: manual reset Against overvoltage, protection technology: manual reset		
Connections - Terminals	Screw connection: 0.752.5 mm ² , (AWG 18AWG 14) without wire end ferrule Screw connection: 0.751.5 mm ² , (AWG 18AWG 16) with wire end ferrule		
Line And Load Regulation	< 0.5 % at 0 to 100 % load at 25 °C < 1 % at full voltage range in line at 25 °C		
Status Led	1 LED (green) output voltage		
Depth	159 mm		
Height	30 mm		
Width	97 mm		
Net Weight	0.36 kg		
Output Coupling	Parallel Serial		
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 Double-profile DIN rail panel mounting		
Supply	SELV conforming to IEC 60950-1 SELV conforming to IEC 60204-1 SELV conforming to IEC 60364-4-41		
Dielectric Strength	3750 V AC with input to output		
Service Life	10 year(s)		
Overvoltage Category	11		

Environment

Standards	IEC 62368-1
	EN/IEC 61010-1
	EN 61010-2-201
	EN/IEC 61204-3
	IEC 61000-6-1
	IEC 61000-6-2
	IEC 61000-6-3
	IEC 61000-6-4
	IEC 61000-3-2
	EN 61000-3-3
	UL 62368-1
	UL 61010-1
	UL 61010-2-201
	CSA C22.2 No 62368-1
	CSA C22.2 No 61010-1
	CSA C22.2 No 61010-2-201
	IEC 60335-1
	EN/IEC 62368-1
Product Certifications	CE
	CULus
	EAC
	RCM
	CB Scheme
	KC
Operating Altitude	5000 m
Shock Resistance	150 m/s² for 11 ms
Ip Degree Of Protection	IP10
Ambient Air Temperature For	-3025 °C with current derating of 4 % per °C mounting position B, G < 2000 m
Operation	-2550 °C without derating mounting position B, G < 2000 m
	5070 °C with current derating of 2 % per °C mounting position B, G < 2000 m
Electrical Shock Protection Class	Class I
Pollution Degree	2

Vibration Resistance	3 mm (f= 29 Hz) conforming to IEC 60068-2-6
	10 m/s ² (f= 9200 Hz) conforming to IEC 60068-2-6
Electromagnetic Immunity	Immunity to electrostatic discharge - test level: 8 kV (contact discharge) conforming to IEC 61000-4-2
	Immunity to electrostatic discharge - test level: 15 kV (air discharge) conforming to IEC 61000-4-2
	Immunity to conducted RF disturbances - test level: 15 V/m (80 MHz2 GHz) conforming to IEC 61000-4-3
	Immunity to conducted RF disturbances - test level: 5 V/m (22.7 GHz) conforming to IEC 61000-4-3
	Immunity to conducted RF disturbances - test level: 5 V/m (2.76 GHz) conforming to IEC 61000-4-3
	Immunity to fast transients - test level: 4 kV (on input-output) conforming to IEC 61000-4-4
	Surge immunity test - test level: 4 kV (between power supply and earth) conforming to IEC 61000-4-5
	Surge immunity test - test level: 3 kV (between phases) conforming to IEC 61000-4-5 Immunity to conducted RF disturbances - test level: 15 V (0.1580 MHz) conforming to IEC 61000-4-6
	Immunity to magnetic fields - test level: 30 A/m (5060 Hz) conforming to IEC 61000-4-8
	Immunity to voltage dips conforming to IEC 61000-4-11 Disturbing field emission conforming to EN 55016-2-3
	Limits for harmonic current emissions conforming to IEC 61000-3-2 conforming to EN 55016-1-2 conforming to EN 55016-2-1
Electromagnetic Emission	Conducted emissions conforming to IEC 61000-6-3 Radiated emissions conforming to IEC 61000-6-4

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	14.600 cm
Package 1 Length	21.500 cm
Package 1 Weight	490.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	17
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.890 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration Pro-active compliance (Product out of EU RoHS legal scope)		
Eu Rohs Directive			
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

Dimensions Drawings


Electrical Safety

- If the unit is use in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.
- For means of disconnection a switch or circuit breaker, located near the product, must be included in the installation. A marking as disconnecting device for the product is required.
- The device has an internal fuse. The unit is tested and approved with branch circuit protective device up to 20A. This circuit breaker can be used as disconnecting device.
- The power supply is only suitable for audio, video, information, communication, industrial and control equipment.

Dimensions

Front and Side Views






Connections and Schema


Connections and Schema

Correct Parallel Connection






Incorrect Parallel Connection




(1) : Load ABLx1Axxxxx-1 = ABLx1Axxxxx-2 max 2 x ABLx1Axxxxx L1 = L2 ΔV max 25 mV $I_{Load} < 90\% 2 x I_{nom}$

Output Voltage Balancing



(1): R_{Load1} (2): R_{Load2} $R_{Load1} = R_{Load2}$ $I_1 = I_2 = ~ I_{nom}$





(1) : V_{out1}

- (2) : V_{out2}
- (3) : 2 x Diode, V_{RRM} > 2 x $V_{out1/2}$, I_F > 2 x $I_{nom1/2}$
- (4) : V_{Load} = 2 x V_{out}
- (5) : Load

Connections and Schema


	(1)		
	<40°C	<50°C	<70°C
ABLP1A12085	60°C	70ºC	90°C
ABLP1A24045	60°C	70°C	90°C
ABLP1A24062	60ºC	70ºC	90°C
ABLP1A24100	60°C	70ºC	90°C

(1) : Ambient


Mounting and Clearance

Mounting


Mounting Position B




Mounting Position F




Mounting Position G






Mounting Position H



Performance Curves

Performance Curves


Mounting Position B and G



Mounting Position F

Υ -30 -20 -10 Х

Mounting Position H



X : Surrounding Air Temperature (°C)

Y: Percentage of Max Load (%)

1 : Altitude 2000 m

2 : Altitude 5000 m

Note : < 100 VAC additional derating by 1.33% / VAC