Product datasheet

Specifications





Push button, Harmony 9001K, metal, mushroom 41mm, red, 30mm, 2 positions, push pull, 1NC

9001KR9RH6

Main

mann	
Range Of Product	Harmony 9001K
Product Or Component Type	Push-button
Device Short Name	9001K
Type Of Operator	push-pull
Operator Profile	Red mushroom Ø 41 mm, unmarked

Complementary	
Bezel Material	Metal
Mounting Diameter	30 mm
Cad Overall Width	54 mm
Cad Overall Height	103 mm
Cad Overall Depth	74 mm
Net Weight	0.141 kg
Operating Position	Any position
Shape Of Signaling Unit Head	Round
Head Material	Plastic
Operator Additional Information	Screw-on plastic
Operator Position Information	2 positions
Contacts Type And Composition	1 NC
Positive Opening	With conforming to IEC 60947-5-2
Mechanical Durability	5000000 cycles
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm ² conforming to IEC 60947-1
Tightening Torque	0.8 N.m conforming to IEC 60947-1
Shape Of Screw Head	Cross slotted
Contacts Material	Silver alloy contacts
Short-Circuit Protection	10 A cartridge fuse conforming to IEC 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A
[Ui] Rated Insulation Voltage	250 V (pollution degree 3) conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	2.5 kV conforming to IEC 60947-1
[Ie] Rated Operational Current	3 A at 240 V, AC-15, A600-Q600 conforming to NEMA

0.55 A at 125 V, DC-13, A600-Q600 conforming to NEMA

[Icm] Rated Short-Circuit Making Capacity	12 kA at 120 V AC-15, 7200 VA 0.1 kA at 600 V DC-13
	0.27 kA at 250 V DC-13
	0.55 kA at 125 V DC-13
Rated Breaking Capacity	3 kA at 240 V AC-15, 720 VA
	6 kA at 120 V AC-15, 720 VA
	1.2 kA at 600 V AC-15, 720 VA
	1.5 kA at 480 V AC-15, 720 VA
	0.1 kA at 600 V DC-13
	0.27 kA at 250 V DC-13
	0.55 kA at 125 V DC-13
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Red
Operator Profile	Mushroom Ø 41 mm
Type Of Operator	Push-pull
Size	30 mm

Environment

Protective Treatment	TC				
Ambient Air Temperature For Storage	-4070 °C				
Ambient Air Temperature For Operation	-2570 °C				
Overvoltage Category	Class II conforming to IEC 61140				
Ip Degree Of Protection	IP66 conforming to IEC 60529				
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 6				
Standards	IEC 60947-5-1 IEC 60947-1 IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508 CSA C22.2 No 14				
Product Certifications	NEMA UL 508				
Vibration Resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6				
Shock Resistance	50 gn conforming to IEC 60068-2-27				

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	4.700 cm
Package 1 Length	9.200 cm
Package 1 Weight	141.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	16

Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.258 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information


Certifications & Standards

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			
Circularity Profile	No need of specific recycling operations			

Product datasheet

Dimensions Drawings

Dimensions




e panel thickness: 1 to 6 mm / 0.04 to 0.24 in. a 32 mm / 1.26 in.

Mounting and Clearance

Contact Block Mounting Position

Top and Rear views




(1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)

- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

Product datasheet

Panel Cut-Out

Clearance



Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

Individual Cut-outs Details

2 alternatives

