

Product datasheet

Specifications



Changeover relay iRLI 10A 2P Uc 24VAC Ue 250VAC

A9E15537

Main

Range Of Product	Acti9
Product Name	Acti9 iRLI
Product Or Component Type	Relay
Device Short Name	iRLI
Device Application	Changeover relay
Signal Contacts Composition	1 C/O + 1 NO
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz

Complementary

[Ie] Rated Operational Current	10 A at 230 V AC (cos Phi = 1)
[Ui] Rated Insulation Voltage	250 V AC
Supply Holding Power	4 VA
Supply Inrush Power	4 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	2
Height	88 mm
Width	18 mm
Depth	70 mm
Net Weight	0.112 kg
Colour	White
Electrical Durability	AC-21: 100000 cycles
Connections - Terminals	Tunnel type terminals 0.5...6 mm²

Environment

Standards	NF C 45-250 IEC 255
Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-5...55 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.200 cm
Package 1 Width	1.700 cm
Package 1 Length	8.500 cm
Package 1 Weight	116.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.000 cm
Package 2 Width	9.300 cm
Package 2 Length	22.800 cm
Package 2 Weight	1.438 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	17.740 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins