





Usually in Stock

# APC Back-UPS 700VA, 230V, AVR, IEC Sockets (To be replace by BX750MI)

BX700UI

! Discontinued on: 21 Dec 2023

! End-of-service on: 21 Dec 2023

## Discontinued - Service only

## Overview

Lead Time

Main	
Main Input Voltage	230 V
Rated Power In W	390 W
Rated Power In Va	700 VA
Output Connection Type	4 IEC 60320 C13

 Cable Length
 1.22 m

Number Of Cables 1

Battery Type Lead-acid battery

## **Batteries & Runtime**

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	6 h
Number Of Battery Replacement Quantity	1
Battery Voltage	12 V
Battery Capacity	7.0 Ah
Battery Charger Power	14 W rated
Battery Life	35 year(s)
Replacement Battery	APCRBC110 ☐
Battery Graph Comments	This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several v
Extended Runtime	0

#### General

Provided Equipment user manual

Product Web Sub-Family	Entry level
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

# **Physical**

Height	20 cm
Width	11.5 cm
Depth	25.6 cm
Net Weight	6 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	Yes

## Input

Network Frequency	50/60 Hz +/- 3 Hz auto-sensing
Input Voltage Limits	140300 V
Switching Current Capacity	7 A

# Output

Maximum Configurable Power In W	390 W
Output Frequency	50/60 Hz +/- 1 Hz sync to mains
Ups Type	Line interactive
Wave Type	Stepped approximation to a sinewave
Maximum Configurable Power In Va	700 VA
Transfer Time	4 ms typical

## **Environmental**

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 % non-condensing
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-1540 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.009144.00 m
Acoustic Level	45 dBA

# **Communications & Management**

Control Panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone

# **Surge Protection and Filtering**

Surge Energy Rate 273 J

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27.5 cm
Package 1 Width	34 cm
Package 1 Length	29.5 cm
Package 1 Weight	6.5 kg
Scc14	10731304315800

## **Contractual warranty**

Warranty 2 years repair or replace

## Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

## Resource performance



**Energy Efficient Product** 



Take-Back Program Available

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

16 May 2024