Product datasheet

Specifications

Residual current circuit breaker (RCCB), Acti9 iID, 4P, 63A, AC type, 300mA

A9R74463

Main

Range	Acti9
Product Name	Acti9 iID
Product Or Component Type	Residual current circuit breaker (RCCB)
Device Short Name	iID
Poles Description	4P
Neutral Position	Left
[In] Rated Current	63 A
Network Type	AC
Earth-Leakage Sensitivity	300 mA
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Type AC

Complementary

Device Location In System	Outgoer
Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	380...415 V AC 50/60 Hz
Residual Current Tripping Technology	Voltage independent
Rated Breaking And Making Capacity	Idm 1500 A Im 1500 A
Rated Conditional Short-Circuit Current	10 kA
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
Contact Position Indicator	Yes
Control Type	Toggle
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	8
Height	91 mm
Width	72 mm
Depth	73.5 mm
Net Weight	0.37 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	AC-1: 15000 cycles
Locking Options Description	Padlocking device
Connections - Terminals	Single terminal top or bottom 1…35 mm² rigid Single terminal top or bottom 1…25 mm² flexible Single terminal top or bottom 1…25 mm² flexible with ferrule
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	3.5 N.m top or bottom

Environment

Standards	EN/IEC 61008-1
Product Certifications	SNI
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3
Electromagnetic Compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61008-1
Ambient Air Temperature For Operation	-5…60 °C
Ambient Air Temperature For Storage	-40…85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.400 cm
Package 1 Width	7.700 cm
Package 1 Length	9.800 cm
Package 1 Weight	358.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	27
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.204 kg

Contractual warranty

Warranty	18 months

Sustainability

Green Premium^{TM} label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency

RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations