



Acti9 Smartlink SI B - Modbus TCP/IP and Wireless communication module

A9XMZA08

Main

Range Of Product	Acti9	
Product Name	Acti9 Smartlink	
Product Or Component Type	Smart communication module	
Device Short Name	Smartlink SI B Ethernet	
Application Type	Basic energy metering E Improved load monitoring E, U, I, P, Pf Load alarming Load control Breaker status monitoring	
Number Max Of Connected Devices	Up to 7 wired devices Up to 20 wireless devices	
Group Of Channels	1 group of 7 digital channels 1 group of 1 analog channel	
Maximum Supply Current	1.5 A	
[Us] Rated Supply Voltage	24 V DC +/- 20 %	
Connectivity To Devices	Analog input Digital input and output Pulse output meter Wireless energy sensor	
Communication Service	Ethernet Modbus TCP/IP server Web server	
Web Server	BMS controller compatible Embedded web page	
Transmission Support Medium	Radio frequency 2.42.4835 GHz PowerTag 20	
Web Services	Web page	

Complementary

Application Specific I/O	Pulse converter Pulse totalising counter	
Protection Type	Short-circuit protection for analog input Against reverse polarity for auxiliary supply Against reverse polarity for input Overvoltage at 33 V DC for digital output	
Immunity To Microbreaks	10 ms	
Reset	Factory reset on front face	
Input/Output Type	2 inputs per analog channel 2 inputs + 1 output per digital channel	
Input Type	Current for analog input, 420 mA Voltage for analog input, 010 V DC Current sink for digital input, 24 V DC +/- 20 % at 2.5 mA	

Maximum Permanent Current	0.005 A for digital input	
Absolute Accuracy Error	+/- 1 % of full scale for analog input 12 bits	
Electronic Filtering Time	2 ms for digital input from state 0 to state 1 2 ms for analog input from state 0 to state 1	
Output Type	Logic current source: 24 V - DC - 100 mA	
Maximum Voltage Drop	<1 V at state 1 digital output	
Inrush Current	0.5 A for digital output 3 A for power supply	
Local Signalling	Communication: 1 LED (yellow) NS (Network Status): 1 LED (green, orange and red) Communication (LK/ACT 10/100): 1 LED (green and yellow) Status: 1 LED (green, orange and red)	
Mounting Position	Horizontal and vertical on DIN rail	
Colour	White (RAL 9003)	
Location Of Connection	Front	
Connections - Terminals	Spring-loaded terminal Ti24 qty: 7 for digital input/output, ordered separately RJ45 connector qty: 1 for ETHERNET, ordered separately Plug-in connector qty: 1 for supply circuit Plug-in connector qty: 1 for communication bus Plug-in connector qty: 1 for analog input	
Clamping Connection Capacity	2 x 0.25 mm² for twisted shielded pairs cable, flexible with cable end for communication bus 2 x 0.25 mm² for twisted shielded pairs cable, flexible without cable end for communication bus 2 x 0.25 mm² for twisted shielded pairs cable, rigid with cable end for communication bus 2 x 0.25 mm² for twisted shielded pairs cable, rigid without cable end for communication bus 2 x 0.25 mm² for twisted shielded pairs cable, rigid without cable end for communication bus 2 x 0.252 x 1.5 mm² for twisted shielded pairs cable, rigid with cable end for analog input 2 x 0.252 x 1.5 mm² for twisted shielded pairs cable, rigid without cable end for analog input 2 x 0.252 x 1.5 mm² for twisted shielded pairs cable, flexible with cable end for analog input 2 x 0.252 x 1.5 mm² for twisted shielded pairs cable, flexible without cable end for analog input 1 x 0.51 x 1.5 mm², flexible with cable end for control 1 x 0.51 x 1.5 mm², flexible without cable end for control 1 x 0.51 x 1.5 mm², rigid with cable end for control 2 x 0.22 x 1.5 mm², flexible with cable end for supply circuit 2 x 0.22 x 1.5 mm², rigid with cable end for supply circuit 2 x 0.22 x 1.5 mm², rigid with cable end for supply circuit 2 x 0.22 x 1.5 mm², rigid without cable end for supply circuit	
Wire Stripping Length	Control: 10 mm Supply circuit: 7 mm Analog input: 7 mm Communication bus: 7 mm	
Communication Network Type	RS485 Modbus RTU master SUB-D 9 9.619.2 kbauds Ethernet Modbus TCP/IP server RJ45 10/100 Mbit/s	
9 Mm Pitches	0 useful	
Height	22.5 mm	
Width	359 mm	
Depth	42 mm	
Net Weight	180 g	
Provided Equipment	Set of 1 connector Set of 1 bus connector Set of 1 power supply connector Set of 2 locking clips	

Range Compatibility	Acti 9 iTL auxiliary		
	Multi9 C60		
	Linergy Linergy FM		
	Acti 9 iOF+SD 24		
	Acti 9 iACT24		
	Acti 9 iATL24 PowerLogic pulse output meter		
	PowerLogic Modbus meter		
	Acti 9 PowerTag wireless energy sensor		
	Acti 9 RCA iC60 Acti 9 Acti9 iCT auxiliary Acti 9 Acti9 iC60		
			Acti 9 Acti9 iID Acti 9 Acti9 iSW-NA Acti 9 Acti9 iDPN Vigi Acti 9 Acti9 C40
	Acti 9 Acti9 DT60		
		Acti 9 Acti9 I-NA	
		Acti 9 Acti9 ITG40	
		Acti 9 Acti9 iDPN	
		Acti 9 Acti9 Reflex iC60 Ti24 connector	
	Commissioning Interface	ECOREACH	
	Web page		
Compatibility Code	Acti 9 Smartlink IP		

Environment

Ip Degree Of Protection	IP20	
Pollution Degree	3	
Electromagnetic Compatibility	Resistance to electrostatic discharge (air discharge), 8 kV, conforming to IEC 61000-4-2	
	Resistance to electrostatic discharge (contact discharge), 4 kV, conforming to IEC 61000-4-2	
	Resistance to radiated electromagnetic fields (80 MHz3 GHz), 10 V/m, conforming to IEC 61000-4-3	
	Power supply: resistance to fast transient (5100 kHz), 2 kV, conforming to IEC 61000-4-4	
	Input/output: resistance to fast transient, 1 kV, conforming to IEC 61000-4-4 Communication bus: resistance to fast transient, 1 kV, conforming to IEC 61000-4-4 Conducted EMC (0.1580 MHz), 10 V, conforming to IEC 61000-4-6	
	Immunity to magnetic fields at network frequency, 30 A/m, conforming to IEC 61000-4-8	
	Radiated emission (301000 MHz), class A, conforming to IEC 61131-3 Ed.3 Conducted emission (0.1530 MHz), class A, conforming to IEC 61131-2	
Environmental Characteristic	Corrosive 3C2 conforming to IEC 60721-3-3 Salt mist 2 conforming to IEC 60068-2-52	
Vibration Resistance	1 gn, amplitude = 3.5 mm (f = 5300 Hz)10 cycles conforming to IEC 60068-2-6	
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27	
Fire Resistance	Other parts: 650 °C (30 s) conforming to IEC 60695-2-10 On connection terminals: 960 °C (30 s) conforming to IEC 60695-2-10	
Tropicalisation	2	
Relative Humidity	93 % at 40 °C	
Operating Altitude	02000 m	
Ambient Air Temperature For Operation	-2560 °C	
Ambient Air Temperature For Storage	-4080 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.400 cm

Package 1 Width	6.300 cm
Package 1 Length	36.700 cm
Package 1 Weight	304.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	32
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.215 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information