Product datasheet

Specification





passive connection sub-base ABE7 - 16 inputs or outputs - Led

ABE7H16C11

Main

Range Of Product	Modicon ABE7
Product Or Component Type	Passive discrete I/O sub-base
Sub-Base Type	Miniature sub-base
[Us] Rated Supply Voltage	1930 V conforming to IEC 61131-2
Number Of Channels	16
Number Of Terminal Per Channel	1
Connections - Terminals	Screw type terminals, 1 x 0.091 x 1.5 mm², 0.091.5 mm² (AWG 28AWG 16) flexible with cable end Screw type terminals, 1 x 0.141 x 2.5 mm², 0.142.5 mm² (AWG 26AWG 12) solid
	Screw type terminals, 1 x 0.141 x 2.5 mm², 0.142.5 mm² (AWG 26AWG 14) flexible without cable end Screw type terminals, 2 x 0.092 x 0.75 mm², 0.090.75 mm² (AWG 28AWG 20) flexible with cable end
	Screw type terminals, 2 x 0.22 x 2.5 mm², 0.22.5 mm² (AWG 24AWG 14) solid

Complementary

Summly Vallage Time	DO.
Supply Voltage Type	DC
Number Of Horizontal Rows	1
Status Led	1 LED per channel (green) channel status 1 LED (green) power ON
Polarity Distribution	No
Short-Circuit Protection	2 A internal fuse, 5 x 20 mm, fast blow (PLC end)
Fixing Mode	By clips (35 mm symmetrical DIN rail) By screws (solid plate with fixing kit)
Maximum Supply Current	1.8 A
Current Per Channel	0.5 A
Maximum Current Per Output Common	1.8 A
Voltage Drop On Power Supply Fuse	0.3 V
[Ui] Rated Insulation Voltage	2000 V
Installation Category	II conforming to IEC 60664-1
Tightening Torque	0.6 N.m with flat Ø 3.5 mm screwdriver
Net Weight	0.16 kg

Environment

Product Certifications	111
Froduct Certifications	UL
	CSA
	DNV
	GL
	EAC
Ip Degree Of Protection	IP2X conforming to IEC 60529
Resistance To Incandescent Wire	750 °C, extinction time <30 s conforming to IEC 60695-2-11
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27
Vibration Resistance	2 gn (f= 10150 Hz) conforming to IEC 60068-2-6
Resistance To Electrostatic	4 kV (contact) level 3 conforming to IEC 61000-4-2
Discharge	8 kV (air) level 3 conforming to IEC 61000-4-2
2.0090	8 kV (all) level 3 collidifility to IEC 01000-4-2
Resistance To Radiated Fields	10 V/m (260000001000000000 Hz) conforming to IEC 61000-4-3 level 3
Resistance To Fast Transients	2 kV level 3 conforming to IEC 61000-4-4
Ambient Air Temperature For Operation	-560 °C conforming to IEC 61131-2
Ambient Air Temperature For Storage	-4080 °C conforming to IEC 61131-2
Pollution Degree	2 conforming to IEC 60664-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.11 cm
Package 1 Width	8.13 cm
Package 1 Length	13.72 cm
Package 1 Weight	0.15 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	32
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.152 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings


Dimensions



(1) ABE7BV10 / BV20

Mounting and Clearance


Mounting




ABE7H16C11


Connections and Schema

HE10 16 Channels



Wiring Diagram






(1) Inductive load

Performance Curves

Curves for Determining Cable Type and Length According to the Current

16-channel Sub-base



- L Cable length
- I_{T} Total current per sub base (A)
- I_A Average current per channel (mA)
- (1) TSXCDP••2 and ABFH20H••0 cables with c.s.a. 0.08 mm² (AWG 28).
- (2) TSXCDP••3 cables with c.s.a. 0.34 mm² (AWG 22).
- (3) Cables with c.s.a. 0.13 mm² (AWG 26).

The curves are given for a voltage drop of 1 V in the cable. For n volts tolerance, multiply the length determined from the graph by n.