Product datasheet





Regulated Power Supply, modicon power supply, 100...240V AC, 24V, 10A, single phase, Panel Mount

ABLP1A24100

Main

Range Of Product	Modicon Power Supply
Product Or Component Type	Power supply
Power Supply Type	Regulated switch mode
Variant Option	Panel mount
Enclosure Material	Aluminium
Nominal Input Voltage	100240 V AC single phase
Rated Power In W	240 W
Output Voltage	24 V DC
Power Supply Output Current	10 A

Complementary

85264 V AC		
5060 Hz		
TN		
TT		
ΙΤ		
1 mA 240 V AC		
Integrated fuse (not interchangeable) 6.3 A		
35 A at 115 V		
60 A at 230 V		
0.95 at 115 V AC		
0.91 at 230 V AC		
87 % at 230 V AC		
21.626.4 V		
36 W		
< 3.6 A 115 V AC		
< 1.8 A 230 V AC		
<1.2 s		
> 20 ms 115 V AC		
> 40 ms 230 V AC		
8000 µF		
< 150 mV		
700000 h at 25 °C, full load conforming to SR 332		

Life Is On Schneider 17 May 2024

Output Protection Type	Against overload and short-circuits, protection technology: automatic reset Against over temperature, protection technology: manual reset Against overvoltage, protection technology: manual reset		
Connections - Terminals	Screw connection: 0.752.5 mm², (AWG 18AWG 14) without wire end ferrule Screw connection: 0.751.5 mm², (AWG 18AWG 16) with wire end ferrule		
Line And Load Regulation	< 0.5 % at 0 to 100 % load at 25 °C < 1 % at full voltage range in line at 25 °C		
Status Led	1 LED (green) output voltage		
Depth	190 mm		
Height	50 mm		
Width	93 mm		
Net Weight	0.85 kg		
Output Coupling	Parallel Serial		
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 Double-profile DIN rail panel mounting		
Supply	SELV conforming to IEC 60950-1 SELV conforming to IEC 60204-1 SELV conforming to IEC 60364-4-41		
Dielectric Strength	3000 V AC with input to output		
Service Life	10 year(s)		
Overvoltage Category	II		

Environment

Chandanda	150 00000 4				
Standards	IEC 62368-1				
	EN/IEC 61010-1				
	EN 61010-2-201				
	EN/IEC 61204-3				
	IEC 61000-6-1				
	IEC 61000-6-2				
	IEC 61000-6-3				
	IEC 61000-6-4				
	IEC 61000-3-2				
	EN 61000-3-3				
	UL 62368-1				
	UL 61010-1				
	UL 61010-2-201				
	CSA C22.2 No 62368-1				
	CSA C22.2 No 61010-1 CSA C22.2 No 61010-2-201 IEC 60335-1				
	EN/IEC 62368-1				
	EN/IEG 02300-1				
Product Certifications	CE				
	CULus				
	EAC				
	RCM				
	CB Scheme				
	KC				
Operating Altitude	5000 m				
Shock Resistance	150 m/s² for 11 ms				
Ip Degree Of Protection	IP10				
Ambient Air Temperature For	-1050 °C without derating mounting position A, B, C, D, F, G < 2000 m				
Operation	5070 °C with current derating of 2.5 % per °C mounting position A, B, C, D, F, G				
	2000 m				
	5070 °C with current derating of 2.5 % per ♦ ♦ C < 2000 m				
Electrical Shock Protection Class	Class I				

Pollution Degree	2 3 mm (f= 29 Hz) conforming to IEC 60068-2-6 10 m/s² (f= 9200 Hz) conforming to IEC 60068-2-6		
Vibration Resistance			
Electromagnetic Immunity	Immunity to electrostatic discharge - test level: 8 kV (contact discharge) conforming to IEC 61000-4-2 Immunity to electrostatic discharge - test level: 15 kV (air discharge) conforming to IEC 61000-4-2 Immunity to conducted RF disturbances - test level: 15 V/m (80 MHz2 GHz) conforming to IEC 61000-4-3 Immunity to conducted RF disturbances - test level: 5 V/m (22.7 GHz) conforming to IEC 61000-4-3 Immunity to conducted RF disturbances - test level: 5 V/m (2.76 GHz) conforming to IEC 61000-4-3 Immunity to fast transients - test level: 4 kV (on input-output) conforming to IEC 61000-4-4 Surge immunity test - test level: 4 kV (between power supply and earth) conforming to IEC 61000-4-5 Surge immunity test - test level: 3 kV (between phases) conforming to IEC 61000-4-5 Immunity to conducted RF disturbances - test level: 15 V (0.1580 MHz) conforming to IEC 61000-4-6 Immunity to magnetic fields - test level: 30 A/m (5060 Hz) conforming to IEC 61000-4-8 Immunity to voltage dips conforming to IEC 61000-4-11 Disturbing field emission conforming to IEC 61000-3-2 conforming to EN 55016-1-2 conforming to EN 55016-1-2 conforming to EN 55016-2-1		
Electromagnetic Emission	Conducted emissions conforming to IEC 61000-6-3 Radiated emissions conforming to IEC 61000-6-4		

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	14.000 cm
Package 1 Length	24.500 cm
Package 1 Weight	984.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	9
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.269 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	72
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	82.152 kg

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

Product datasheet

ABLP1A24100


Dimensions Drawings


Electrical Safety

- If the unit is use in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.
- For means of disconnection a switch or circuit breaker, located near the product, must be included in the installation. A marking as disconnecting device for the product is required.
- The device has an internal fuse. The unit is tested and approved with branch circuit protective device up to 20A. This circuit breaker can be used as disconnecting device.
- The power supply is only suitable for audio, video, information, communication, industrial and control equipment.

Dimensions

Front and Side Views






Connections and Schema


Connections and Schema

Correct Parallel Connection



(1): Load


Incorrect Parallel Connection



(1) : Load ABLx1Axxxxx-1 = ABLx1Axxxxx-2 max 2 x ABLx1Axxxxx L1 = L2 Δ V max 25 mV I_{Load} < 90% 2 x I_{nom}


Output Voltage Balancing

ABLP1A24100



- (1): R_{Load1}
- (2): R_{Load2}
- $R_{Load1} = R_{Load2}$
- $I_1 = I_2 = \sim I_{\text{nom}}$

Series Connection



- (1): V_{out1}
- (2) : V_{out2}
- (3) : 2 x Diode, V_{RRM}> 2 x V_{out1/2}, I_F > 2 x I_{nom1/2}
- (4) : V_{Load} = 2 x V_{out}
- (5) : Load

Connections and Schema


	(1)		
	<40°C	<50°C	<70°C
ABLP1A12085	60°C	70°C	90°C
ABLP1A24045	60°C	70°C	90°C
ABLP1A24062	60°C	70°C	90°C
ABLP1A24100	60°C	70°C	90°C

(1): Ambient


Mounting and Clearance

Mounting

Mounting Position A




Mounting Position B




Mounting Position C


ABLP1A24100




Mounting Position D1




Mounting Position D2 and F



Mounting Position G






Performance Curves

Performance Curves

Mounting Positions A, B, C, D, F and G



X : Surrounding Air Temperature (°C)
Y : Percentage of Max Load (%)

1 : Altitude 2000 m 2 : Altitude 5000 m

Note : < 100 VAC additional derating by 1.33% / VAC