Product datasheet







Cam switch, Harmony K, Ø 22mm, plastic, 3 poles, 2 positions, 45°, 20A, 45x45mm, metallic legend, marked 0/1, 35mm black handle

K2C003ACH

Main

Range Of Product	Harmony K	
Product Or Component Type	Complete cam switch	
Component Name	K2	
[Ith] Conventional Free Air Thermal Current	20 A	
Mounting Location	Front	
Fixing Mode	Ø 22 mm hole	
Cam Switch Head Type	With front plate 45 x 45 mm	
Type Of Operator	Black handle, length = 35 mm	
Rotary Handle Padlocking	andle Padlocking Without	
Presentation Of Legend	With metallic legend, 0 - 1 black marking	
Cam Switch Function	Switch	
Return	Without	
Off Position	With Off position	
Poles Description	escription 3P	
Switching Positions	Positions Right: 0° - 45°	
Ip Degree Of Protection IP65 conforming to IEC 60529		

Complementary

Switching Angle	45 °	
[Ui] Rated Insulation Voltage	oltage 690 V (pollution degree 3) conforming to IEC 60947-1	
[Ithe] Conventional Enclosed Thermal Current	16 A	
Electrical Durability	200000 cycles AC-23 200000 cycles AC-3	
	600000 cycles AC-15	
	600000 cycles AC-21	
Maximum Operating Rate	2.5 cyc/mn AC-21	
	2.5 cyc/mn AC-23	
	2.5 cyc/mn AC-3	
	8.333 cyc/mn AC-15	
Short-Circuit Current	10000 A	
Short-Circuit Protection	20 A cartridge fuse, type gG	
[Uimp] Rated Impulse Withstand Voltage		
Contact Operation	Slow-break	

Positive Opening	With	
Electrical Connection	Captive screw clamp terminals flexible, clamping capacity: 2 x 1.5 mm ² Captive screw clamp terminals solid, clamping capacity: 1 x 2.5 mm ²	
Mechanical Durability	chanical Durability 1000000 cycles	
Cad Overall Width	45 mm	
Cad Overall Height	III Height 50 mm	
Cad Overall Depth	verall Depth 59 mm	
Net Weight	0.153 kg	

Environment

Standards	IEC 60947-3 for power circuit IEC 60947-5-1 for control circuit CENELEC EN 50013 GB/T 14048.5 for control circuit GB/T 14048.3 for power circuit	
Product Certifications	CSA 240 V 3 hp 3 phases 2 -pole(s) UL 240 V 0.33 hp 1 phase 2 -pole(s) CSA 240 V 1 hp 1 phase UL 240 V 1 hp 3 phases CCC	
Protective Treatment	тс	
Ambient Air Temperature For Operation	-2555 °C	
Ambient Air Temperature For Storage	-4070 °C	
Shock Resistance	30 gn conforming to IEC 68-2-27	
Vibration Resistance	ance 5 gn conforming to IEC 68-2-6 (f = 10150 Hz)	
Overvoltage Category Class II conforming to IEC 536 Class II conforming to NF C 20-030		

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	6.500 cm
Package 1 Length	11.000 cm
Package 1 Weight	163.200 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.501 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	320
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm

Package 3 Weight

64.023 kg

Contractual warranty

Warranty

12 May 2024

18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations