Product datasheet





Auxiliary contact block, TeSys Deca, 4NC, front mounting, lugsring terminals

LADN046

Main

wain		
Range	TeSys	
	TeSys Deca	
Product Name	TeSys Deca	
Product Or Component Type	Auxiliary contact block	
Device Short Name	LADN	
Range Compatibility	TeSys D CAD	
	TeSys D LC1D	
	TeSys F LC1F	
	TeSys F CR1F	
	TeSys Deca CAD	
	TeSys Deca LC1D	
Mounting Location	Front	
Pole Contact Composition 4 NC		
Contacts Operation	Instantaneous	
[Ue] Rated Operational Voltage	690 V AC 25400 Hz	
[le] Rated Operational Current	6 A at 120 V AC-15	
	1.04 A at 690 V AC-15	
	0.55 A at 125 V DC-13	
	0.1 A at 600 V DC-13	
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-5-1	
	600 V conforming to UL 60947-5-1	
	600 V conforming to CSA C22.2 No 60947-5-1	
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C)	
Standards	EN/IEC 60947-5-1	
	UL 60947-5-1	
	CSA C22.2 No 60947-5-1	
	GB/T 14048.5	
Product Certifications	IECEE CB Scheme	
	UL	
	CSA	
	CCC	
	UKCA	

Complementary

Irms Rated Making Capacity	140 A AC conforming to IEC 60947-5-1 250 A DC conforming to IEC 60947-5-1	
Permissible Short-Time Rating	100 A 60 °C 1 s 120 A 60 °C 500 ms 140 A 60 °C 100 ms	
Protection Type	GG fuse 10 A	
Mechanical Durability	30 Mcycles	

Life Is On Schneider 17 May 2024

Minimum Switching Current	5 mA	
Minimum Switching Voltage	17 V	
Non-Overlap Time	1.5 ms on de-energisation no overlap between NC and NO contact 1.5 ms on energisation no overlap between NC and NO contact	
Insulation Resistance	> 10 MOhm	
Connections - Terminals	s - Terminals Lugs-ring terminals (external diameter: 8 mm)	
Tightening Torque	1.7 N.m - with screwdriver flat Ø 6 mm M3.5 1.7 N.m - with screwdriver Philips No 2 M3.5 1.7 N.m - with screwdriver pozidriv No 2 M3.5	
Height	48 mm	
Width	44 mm	
Depth	42 mm	
Net Weight	/eight 0.05 kg	
Colour	Dark grey	

Environment

Environmental Characteristic	Normal environment
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068
Ambient Air Temperature For Storage	-6080 °C
Ambient Air Temperature For Operation	-560 °C
Operating Altitude	3000 m

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	4.7 cm
Package 1 Length	4 cm
Package 1 Weight	57 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.3 cm
Package 2 Width	8.3 cm
Package 2 Length	26 cm
Package 2 Weight	574 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	80
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.845 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations