Product datasheet

Specifications





LED bulb, Harmony XVM, super bright, BA15d, green, steady light, 24V AC DC

DL2EDB3SB

Main

Range Compatibility	Harmony XVM Optimum
Accessory / Separate Part Category	Lighting accessory
Accessory / Separate Part Type	Super bright LED
Accessory / Separate Part Destination	Beacon and indicator bank
Bulb Base	BA 15d
Signalling Type	Steady
Signalling Colour	Green
[Us] Rated Supply Voltage	24 V AC/DC
Luminance	900 cd/m²
Sale Per Indivisible Quantity	1

Complementary

Net Weight 0.009 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	6.0 cm
Package 1 Length	8.0 cm
Package 1 Weight	14.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	48
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.116 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	1536
Package 3 Height	75 cm
Package 3 Width	60 cm

Package 3 Length	80 cm
Package 3 Weight	31 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations