Product datasheet

Specification





Contactor, TeSys Deca, 3P(3NO), AC-3/AC-3e, <=440V, 9A, 24V DC coil, screw clamp terminals

LC1D09BD

Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[le] Rated Operational Current	9 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 25 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 9 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V DC

Complementary

•	
Motor Power Kw	2.2 kW at 220230 V AC 50/60 Hz (AC-3) 4 kW at 380400 V AC 50/60 Hz (AC-3) 4 kW at 415440 V AC 50/60 Hz (AC-3) 5.5 kW at 500 V AC 50/60 Hz (AC-3) 5.5 kW at 660690 V AC 50/60 Hz (AC-3) 2.2 kW at 400 V AC 50/60 Hz (AC-4) 2.2 kW at 220230 V AC 50/60 Hz (AC-3e) 4 kW at 380400 V AC 50/60 Hz (AC-3e) 4 kW at 415440 V AC 50/60 Hz (AC-3e) 5.5 kW at 500 V AC 50/60 Hz (AC-3e) 5.5 kW at 660690 V AC 50/60 Hz (AC-3e)
Motor Power Hp	1 hp at 230/240 V AC 50/60 Hz for 1 phase motors 2 hp at 200/208 V AC 50/60 Hz for 3 phases motors 2 hp at 230/240 V AC 50/60 Hz for 3 phases motors 5 hp at 460/480 V AC 50/60 Hz for 3 phases motors 7.5 hp at 575/600 V AC 50/60 Hz for 3 phases motors 0.33 hp at 115 V AC 50/60 Hz for 1 phase motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	25 A (at 60 °C) for power circuit 10 A (at 60 °C) for signalling circuit
Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947

[Icw] Rated Short-Time Withstand	105 A 40 °C - 10 s for power circuit
Current	210 A 40 °C - 1 s for power circuit
	30 A 40 °C - 10 min for power circuit
	61 A 40 °C - 1 min for power circuit
	·
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
7.0000iatou i aoo ilating	25 A gG at <= 690 V coordination type 1 for power circuit
	20 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit
Power Dissipation Per Pole	1.56 W AC-1
•	0.2 W AC-3
	0.2 W AC-3e
	0.2 W AC-36
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1
-	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	· ·
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	30 Mcycles
Electrical Durability	0.0 Marriage 05 A AO 4 at the 4 AO V
Electrical Durability	0.6 Mcycles 25 A AC-1 at Ue <= 440 V
	2 Mcycles 9 A AC-3 at Ue <= 440 V
	2 Mcycles 9 A AC-3e at Ue <= 440 V
Control Circuit Type	DC standard
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.25 Uc (-4070 °C):drop-out DC
John On July Voltage Limits	
	0.71.25 Uc (-4060 °C):operational DC
	11.25 Uc (6070 °C):operational DC
Inrush Power In W	5.4 W (at 20 °C)
Hold-In Power Consumption In W	5.4 W at 20 °C
Operating Time	63 ±15 % ms closing
Operating fillie	· · · · · · · · · · · · · · · · · · ·
	20 ±20 % ms opening
Time Constant	28 ms
Manipular Constitution Bata	
Maximum Operating Rate	3600 cyc/h 60 °C

Connections - Terminals	Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without cable end		
	Power circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without cable end		
	Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable		
	end Power circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with		
	cable end Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable		
	end Power circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable		
	end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without		
	cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without		
	cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable		
	end		
	Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: flexible with cable end		
	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end		
	Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end		
Tightening Torque	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2		
Auxiliary Contact Composition	1 NO + 1 NC		
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1		
Signalling Circuit Frequency	25400 Hz		
Minimum Switching Voltage	17 V for signalling circuit		
Minimum Switching Current	5 mA for signalling circuit		
nsulation Resistance	> 10 MOhm for signalling circuit		
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact1.5 ms on energisation between NC and NO contact		
Mounting Support	Plate		
	Rail		
Environment			
Standards	CSA C22.2 No 14		
	EN 60947-4-1 EN 60947-5-1		
	IEC 60947-4-1		
	IEC 60947-5-1 UL 508		
	IEC 60335-1		
Product Certifications	GL		
	BV DNV		
	DNV LROS (Lloyds register of shipping)		
	RINA		
	UL		
	CCC CSA		
	GOST		
	UKCA CB		
p Degree Of Protection	IP20 front face conforming to IEC 60529		
Protective Treatment	reatment TH conforming to IEC 60068-2-30		
otective Treatment TH conforming to IEC 60068-2-30			

Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating	
Operating Altitude	03000 m	
Fire Resistance	Resistance 850 °C conforming to IEC 60695-2-1	
Flame Retardance	ce V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor open (10 Gn for 11 ms) Shocks contactor closed (15 Gn for 11 ms)	
Height	77 mm	
Width	45 mm	
Depth	95 mm	
Net Weight	0.48 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	9.200 cm
Package 1 Length	11.100 cm
Package 1 Weight	523.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.160 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	240
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	137.280 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

LC1D09BD

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

LC1		D09D18	D093D123	D099D129
b		77	99	80
	without cover or add-on blocks	93	93	93
С	with cover, without add-on blocks	95	95	95
c1	with LAD N or C (2 or 4 contacts)	126	126	126
c2	with LA6 DK10	138	138	138
c 3	with LAD T, R, S	146	146	146
	with LAD T, R, S and sealing cover	150	150	150

Product datasheet

LC1D09BD

Connections and Schema

Wiring

