Product datasheet

Specification





Contactor, Tesys Deca, 3P(3NO), AC-3/AC-3e, <=440V 18A, 24V DC coil, screw clamp terminals

LC1D18BD

Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
evice Short Name LC1D	
Contactor Application	Motor control Resistive load
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	18 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 32 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 18 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V DC

Complementary

Motor Power Kw	4 kW at 220230 V AC 50/60 Hz (AC-3) 7.5 kW at 380400 V AC 50/60 Hz (AC-3) 9 kW at 415440 V AC 50/60 Hz (AC-3) 10 kW at 500 V AC 50/60 Hz (AC-3) 10 kW at 660690 V AC 50/60 Hz (AC-3) 4 kW at 400 V AC 50/60 Hz (AC-4) 4 kW at 220230 V AC 50/60 Hz (AC-3e) 7.5 kW at 380400 V AC 50/60 Hz (AC-3e) 9 kW at 415440 V AC 50/60 Hz (AC-3e)
	10 kW at 500 V AC 50/60 Hz (AC-3e) 10 kW at 660690 V AC 50/60 Hz (AC-3e)
Motor Power Hp	1 hp at 115 V AC 50/60 Hz for 1 phase motors 3 hp at 230/240 V AC 50/60 Hz for 1 phase motors 5 hp at 200/208 V AC 50/60 Hz for 3 phases motors 5 hp at 230/240 V AC 50/60 Hz for 3 phases motors 10 hp at 460/480 V AC 50/60 Hz for 3 phases motors 15 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 32 A (at 60 °C) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 300 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	300 A at 440 V for power circuit conforming to IEC 60947

15 May 2024 Life Is On Schneider

[Icw] Rated Short-Time Withstand	145 A 40 °C - 10 s for power circuit
Current	240 A 40 °C - 1 s for power circuit
	40 A 40 °C - 10 min for power circuit
	84 A 40 °C - 1 min for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
	140 A - 100 ms for signaling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
7.0000iatou i uoo itating	50 A gG at <= 690 V coordination type 1 for power circuit
	35 A gG at <= 690 V coordination type 2 for power circuit
	33 A gO at \- 030 V cooldination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 32 A 50 Hz for power circuit
Power Dissipation Per Pole	2.5 W AC-1
	0.8 W AC-3
	0.8 W AC-3e
	0.0 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1
	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	30 Mcycles
Flactuical Demoksiis.	
Electrical Durability	1.65 Mcycles 18 A AC-3 at Ue <= 440 V
	1 Mcycles 32 A AC-1 at Ue <= 440 V
	1.65 Mcycles 18 A AC-3e at Ue <= 440 V
Control Circuit Type	DC standard
Coil Technology	With integral suppression device
Control Circuit Voltage Limits	0.4 0.25 Ha / 40 - 70 °C) drap out DC
Control Official Voltage Littles	0.10.25 Uc (-4070 °C):drop-out DC
	0.71.25 Uc (-4060 °C):operational DC
	11.25 Uc (6070 °C):operational DC
Inrush Power In W	5.4 W (at 20 °C)
Hold-In Power Consumption In W	5.4 W at 20 °C
Operating Time	62 ±45 % mg cloping
Operating Time	63 ±15 % ms closing
	20 ±20 % ms opening
Time Constant	79 mc
	28 ms
Maximum Operating Rate	3600 cyc/h 60 °C

lp Degree Of Protection	GOST UKCA CB IP20 front face conforming to IEC 60529		
	GOST UKCA		
	DNV LROS (Lloyds register of shipping) RINA UL CCC CSA		
Product Certifications	GL BV		
	EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1		
Environment Standards	CSA C22.2 No 14		
Mounting Support	Plate Rail		
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact		
Insulation Resistance	> 10 MOhm for signalling circuit		
Minimum Switching Current	5 mA for signalling circuit		
Minimum Switching Voltage	17 V for signalling circuit		
Signalling Circuit Frequency	type mirror contact 1 NC conforming to IEC 60947-4-1 25400 Hz		
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1		
Auxiliary Contact Composition	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 1 NO + 1 NC		
Fightening Torque	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm		
	end Power circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 1.56 mm² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 1.56 mm² - cable stiffness: solid without cable end		
	cable end Power circuit: screw clamp terminals 1 16 mm² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible with cable		
	cable end Power circuit: screw clamp terminals 2 1.56 mm² - cable stiffness: flexible without		
	Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 1.56 mm² - cable stiffness: flexible without		
	Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end		
	end Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end		
	cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable		
	Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without		

Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating	
Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor open (10 Gn for 11 ms) Shocks contactor closed (15 Gn for 11 ms)	
Height	77 mm	
Width	45 mm	
Depth	95 mm	
Net Weight	0.49 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	9.000 cm
Package 1 Length	11.000 cm
Package 1 Weight	522.500 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.068 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	240
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	137.080 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Compliant with Exemptions		
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	End of Life Information		

LC1D18BD

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

LC1		D09D18	D093D123	D099D129
b		77	99	80
	without cover or add-on blocks	93	93	93
С	with cover, without add-on blocks	95	95	95
c1	with LAD N or C (2 or 4 contacts)	126	126	126
c2	with LA6 DK10	138	138	138
с3	with LAD T, R, S	146	146	146
	with LAD T, R, S and sealing cover	150	150	150

Connections and Schema

Wiring

