Product datasheet

Specifications





Auxiliary contact, TeSys GS, 1 C/ O, 3P, 100/125A, fuse type NFC, sizes 22x58mm, for GS1 GS2 Blown fuse

GS1AF23

Main

Range Of Product	TeSys	
Device Short Name	GS1AF	
Product Or Component Type	Auxiliary contact	
Contact Application	Blown fuse signalling	
Contacts Type And Composition	1 C/O	
Contact Operation	Instantaneous	
[Ith] Conventional Free Air Thermal Current	16 A (at 40 °C)	
[Ie] Rated Operational Current	12 A at 24 V DC-13 2 A at 48 V DC-13 3 A at 400 V AC-15 4 A at 230 V AC-15 0.4 A at 220 V DC-13 0.6 A at 110 V DC-13	

Complementary

Range Compatibility	TeSys TeSys GS fuse-switch disconnector	
Mechanical Durability	30000 cycles	
Electrical Durability	30000 cycles AC-15	
Product Compatibility	GS	
Poles Description	3P	
Switch Rated Current	100 A 125 A	
Fuse Type	NFC DIN	
Fuse Size	22 x 58 mm	
Net Weight	0.033 kg	

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.4 cm
Package 1 Length	14.9 cm
Package 1 Weight	31.0 g
Unit Type Of Package 2	S01

Number Of Units In Package 2	20
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	816.0 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information