Product datasheet





Cam switch, Harmony K, multifixing, plastic, 2 poles, 2 positions, 45°, 12A, 45x45mm, metallic legend, marked 0 1, 35mm black handle

K1B002ALH

Main

Range Of Product	Harmony K	
Product Or Component Type	Complete cam switch	
Component Name	K1	
[Ith] Conventional Free Air Thermal Current	12 A	
Mounting Location	Front	
Fixing Mode	Multifixing	
Cam Switch Head Type	With front plate 45 x 45 mm	
Type Of Operator	Black handle, length = 35 mm	
Rotary Handle Padlocking	Without	
Presentation Of Legend	With metallic legend, 0 - 1 black marking	
Cam Switch Function	Switch	
Return	Without	
Off Position	With Off position	
Poles Description	2P	
Switching Positions	Right: 0° - 45°	
Ip Degree Of Protection	IP40 conforming to IEC 60529	

Complementary

Switching Angle	45 °
[Ui] Rated Insulation Voltage	690 V (pollution degree 3) conforming to IEC 60947-1
[Ithe] Conventional Enclosed Thermal Current	10 A
Rated Operational Power In W	10500 W AC-21 500 660 V 3 phases conforming to IEC 947-3

1100 W AC-3, 230 V 3 phases conforming to IEC 947-3 1500 W AC-23A, 230 V 3 phases conforming to IEC 947-3 1500 W AC-3, 400 V 1 phase conforming to IEC 947-3 1500 W AC-3, 400 V 3 phases conforming to IEC 947-3 1500 W AC-3, 500 V 3 phases conforming to IEC 947-3 1500 W AC-3, 690 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 400 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 500 V 3 phases conforming to IEC 947-3 2200 W AC-23A, 690 V 3 phases conforming to IEC 947-3 4800 W AC-21, 230 V 3 phases conforming to IEC 947-3

600 W AC-3, 230 V 1 phase conforming to IEC 947-3 8300 W AC-21, 400 V 3 phases conforming to IEC 947-3

[le] Rated Operational Current Ac	1.8 A at 690 V AC-3 3 phases conforming to IEC 947-3
	2.8 A at 500 V AC-3 3 phases conforming to IEC 947-3
	2.8 A at 690 V AC-23A 3 phases conforming to IEC 947-3
	3.3 A at 400 V AC-3 3 phases conforming to IEC 947-3
	3.8 A at 500 V AC-23A 3 phases conforming to IEC 947-3 4.6 A at 230 V AC-3 3 phases conforming to IEC 947-3
	4.8 A at 400 V AC-23A 3 phases conforming to IEC 947-3
	5.6 A at 230 V AC-23A 3 phases conforming to IEC 947-3
	1 A at 500 V AC-15 conforming to IEC 947-5-1
	2 A at 400 V AC-15 conforming to IEC 947-5-1
	3 A at 230 V AC-15 conforming to IEC 947-5-1
Electrical Durability	1000000 cycles AC-15
	1000000 cycles AC-21
	500000 cycles AC-23
	500000 cycles AC-3
Maximum Operating Rate	2.5 cyc/mn AC-21
	2.5 cyc/mn AC-23
	2.5 cyc/mn AC-3
	8.333 cyc/mn AC-15
Short-Circuit Current	10000 A
Short-Circuit Protection	16 A cartridge fuse, type gG
[Uimp] Rated Impulse Withstand	4 kV in isolating function
Voltage	6 kV conforming to IEC 947-1
Contact Operation	Slow-break
Positive Opening	With
Electrical Connection	Captive screw clamp terminals flexible, clamping capacity: 2 x 1.5 mm² Captive screw clamp terminals solid, clamping capacity: 1 x 2.5 mm²
Mechanical Durability	1000000 cycles
Cad Overall Width	45 mm
Cad Overall Height	45 mm
Cad Overall Depth	77 mm
Net Weight	0.113 kg
Environment	
Standards	IEC 60047 3 for power circuit
	IEC 60947-3 for power circuit IEC 60947-5-1 for control circuit
	CENELEC EN 50013
	GB/T 14048.5 for control circuit
	GB/T 14048.3 for power circuit
Product Certifications	CSA 240 V 3 hp 3 phases 2 -pole(s)
	UL 240 V 0.33 hp 1 phase 2 -pole(s)
	CSA 240 V 1 hp 1 phase
	UL 240 V 1 hp 3 phases
	CCC
Protective Treatment	TC
Ambient Air Temperature For Operation	-2555 °C
Ambient Air Temperature For Storage	-4070 °C
Shock Resistance	30 gn conforming to IEC 68-2-27
Vibration Resistance	5 gn conforming to IEC 68-2-6 (f = 10150 Hz)
Overvoltage Category	Class II conforming to IEC 536
	Class II conforming to NF C 20-030
Packing Units	

PCE

Unit Type Of Package 1

Number Of Units In Package 1	1	
Package 1 Height	6.500 cm	
Package 1 Width	6.500 cm	
Package 1 Length	11.000 cm	
Package 1 Weight	131.000 g	
Unit Type Of Package 2	S01	
Number Of Units In Package 2	10	
Package 2 Height	15.000 cm	
Package 2 Width	15.000 cm	
Package 2 Length	40.000 cm	
Package 2 Weight	1.441 kg	
Unit Type Of Package 3	P06	
Number Of Units In Package 3	320	
Package 3 Height	75.000 cm	
Package 3 Width	80.000 cm	
Package 3 Length	60.000 cm	
Package 3 Weight	54.112 kg	

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations


Product datasheet

K1B002ALH

Dimensions Drawings

Operating Head and Body

Front Mounting "Multi-Fixing"



- a 53 mm/2.09 in.
- e support panel thickness 1 mm to 6 mm./0.039 in. to 0.24 in.


K1B002ALH

Technical Description

Link Positions (Factory Mounted)

Diagram for 1 to 6-pole Switches

Select the number of poles according to the product characteristics.



- I1 Input 1
- I2 Input 2
- O1 Output 1
- O2 Output 2

Marking




Angular Position of Switch



Switching Program

Diagram for 1 to 6-pole Switches

Select the number of poles according to the product characteristics.



- (1) 1-pole
- (2) 2-pole
- (3) 3-pole
- (4) 4-pole
- (5) 5-pole
- (6) 6-pole

Convention Used for Switching Program Representation

Contact closed

Contact closed in 2 positions and maintained between the 2 positions

Sealed assembly for auto-maintain control

Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

