





Cam switch, Harmony K, Ø 22mm, plastic, 3 poles, 2 positions, 90°, 12A, 45x45mm, metallic legend, marked 0/1, 35mm black handle

K1C003HCH

Main

Range Of Product	Harmony K	
Product Or Component Type	Complete cam switch	
Component Name	K1	
[Ith] Conventional Free Air Thermal Current	12 A	
Mounting Location	Front	
Fixing Mode	Ø 22 mm hole	
Cam Switch Head Type	With front plate 45 x 45 mm	
Type Of Operator	Black handle, length = 35 mm	
Rotary Handle Padlocking	Without	
Presentation Of Legend	With metallic legend, 0 - 1 black marking	
Cam Switch Function	Switch	
Return	Without	
Off Position	With Off position	
Poles Description	3P	
Switching Positions	Right: 0° - 90°	
Ip Degree Of Protection	IP65 conforming to IEC 60529	

Complementary

Switching Angle	90 °	
[Ui] Rated Insulation Voltage	690 V (pollution degree 3) conforming to IEC 60947-1	
[Ithe] Conventional Enclosed Thermal Current	10 A	
Rated Operational Power In W	10500 W AC-21, 500660 V 3 phases conforming to IEC 60947-3	

1 May 2024

1100 W AC-3, 230 V 3 phases conforming to IEC 60947-3 1500 W AC-23A, 230 V 3 phases conforming to IEC 60947-3 1500 W AC-3, 400 V 1 phase conforming to IEC 60947-3 1500 W AC-3, 400 V 3 phases conforming to IEC 60947-3 1500 W AC-3, 500 V 3 phases conforming to IEC 60947-3 1500 W AC-3, 690 V 3 phases conforming to IEC 60947-3 2200 W AC-23A, 400 V 3 phases conforming to IEC 60947-3 2200 W AC-23A, 500 V 3 phases conforming to IEC 60947-3 2200 W AC-23A, 690 V 3 phases conforming to IEC 60947-3 4800 W AC-21, 230 V 3 phases conforming to IEC 60947-3 600~W AC-3, 230 V 1 phase conforming to IEC 60947-38300 W AC-21, 400 V 3 phases conforming to IEC 60947-3

[le] Rated Operational Current Ac	1.8 A at 690 V AC-3 3 phases conforming to IEC 60947-3
	2.8 A at 500 V AC-3 3 phases conforming to IEC 60947-3
	2.8 A at 690 V AC-23A 3 phases conforming to IEC 60947-3
	3.3 A at 400 V AC-3 3 phases conforming to IEC 60947-3
	3.8 A at 500 V AC-23A 3 phases conforming to IEC 60947-3
	4.6 A at 230 V AC-3 3 phases conforming to IEC 60947-3
	4.8 A at 400 V AC-23A 3 phases conforming to IEC 60947-3 5.6 A at 230 V AC-23A 3 phases conforming to IEC 60947-3
	1 A at 500 V AC-15 conforming to IEC 60947-5-1
	2 A at 400 V AC-15 conforming to IEC 60947-5-1
	3 A at 230 V AC-15 conforming to IEC 60947-5-1
	<u> </u>
Electrical Durability	1000000 cycles AC-15
	1000000 cycles AC-21
	500000 cycles AC-23
	500000 cycles AC-3
Maximum Operating Rate	2.5 cyc/mn AC-21
	2.5 cyc/mn AC-23
	2.5 cyc/mn AC-3
	8.333 cyc/mn AC-15
Short-Circuit Current	10000 A
Short-Circuit Protection	16 A cartridge fuse, type gG
[Uimp] Rated Impulse Withstand Voltage	4 kV in isolating function 6 kV conforming to IEC 60947-1
	6 KV Contoining to IEC 60947-1
Contact Operation	Slow-break
Positive Opening	With
Electrical Connection	Captive screw clamp terminals flexible, clamping capacity: $2 \times 1.5 \text{ mm}^2$ Captive screw clamp terminals solid, clamping capacity: $1 \times 2.5 \text{ mm}^2$
Mechanical Durability	1000000 cycles
Cad Overall Width	45 mm
Cad Overall Height	50 mm
Cad Overall Depth	59 mm
Net Weight	0.155 kg
Environment	
Standards	IEC 60947-3 for power circuit
	IEC 60947-5-1 for control circuit
	CENELEC EN 50013
	GB/T 14048.5 for control circuit
	GB/T 14048.3 for power circuit
Product Certifications	CSA 240 V 3 hp 3 phases 2 -pole(s)
	UL 240 V 0.33 hp 1 phase 2 -pole(s)
	CSA 240 V 1 hp 1 phase
	UL 240 V 1 hp 3 phases
	CCC
Protective Treatment	TC
Ambient Air Temperature For	-2555 °C
Operation	40. 70.00
Ambient Air Temperature For Storage	-4070 °C
Shock Resistance	30 gn conforming to IEC 68-2-27
Vibration Resistance	5 gn conforming to IEC 68-2-6 (f = 10150 Hz)
Overvoltage Category	Class II conforming to IEC 536
	Class II conforming to NF C 20-030
Packing Units	

PCE

Unit Type Of Package 1

Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.5 cm
Package 1 Length	11.0 cm
Package 1 Weight	176.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.955 kg

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations


1 May 2024

K1C003HCH

Dimensions Drawings

Operating Head and Body with Plastic Base

Front Mounting by Ø 22 mm/0.87 in. Hole



a1 80.5 mm/3.17 in.

1 May 2024

e support panel thickness 1 mm to 6 mm./0.039 in. to 0.24 in.


K1C003HCH

Technical Description

Link Positions (Factory Mounted)

Diagram for 2 to 4-pole Switches

Select the number of poles according to the product characteristics.



K1C003HCH

Marking



Angular Position of Switch



K1C003HCH

Switching Program

Diagram for 2 to 4-pole Switches

Select the number of poles according to the product characteristics.



- (2) 2-pole
- (3) 3-pole
- (4) 4-pole

Convention Used for Switching Program Representation

Contact closed

Contact closed in 2 positions and maintained between the 2 positions

Sealed assembly for auto-maintain control

Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

10

