





Cam changeover switch, Harmony K, 22mm, plastic, 2 poles, position 0, 45°, 12A, 45x45mm, metallic legend, marked 2 0 1, 35mm black handle

K1D002UCH

#### Main

Range Of Product	Harmony K	
Product Or Component Type	Complete cam switch	
Component Name	K1	
[Ith] Conventional Free Air Thermal Current	12 A	
Product Mounting	Front mounting	
Fixing Mode	Ø 22 mm hole	
Cam Switch Head Type	With front plate 45 x 45 mm	
Type Of Operator	Black handle, length = 35 mm	
Rotary Handle Padlocking	Without	
Presentation Of Legend	With metallic legend, 2 - 0 - 1 black marking	
Cam Switch Function	Changeover switch	
Return	Without	
Off Position	With Off position	
Poles Description	2P	
Switching Positions	Right: 0° - 45° Left: 0° - 315°	
Ip Degree Of Protection	IP65 conforming to IEC 60529	

# Complementary

Switching Angle	45 °
[Ui] Rated Insulation Voltage	690 V (pollution degree 3) conforming to IEC 60947-1
[Ithe] Conventional Enclosed Thermal Current	10 A
Rated Operational Power In W	10500 W AC-21, 500660 V 3 phases conforming to IEC 947-3

1100 W AC-3, 230 V 3 phases conforming to IEC 947-3
1500 W AC-32A, 230 V 3 phases conforming to IEC 947-3
1500 W AC-3, 400 V 1 phase conforming to IEC 947-3
1500 W AC-3, 400 V 3 phases conforming to IEC 947-3
1500 W AC-3, 500 V 3 phases conforming to IEC 947-3
1500 W AC-3, 500 V 3 phases conforming to IEC 947-3
1500 W AC-33, 690 V 3 phases conforming to IEC 947-3
2200 W AC-23A, 500 V 3 phases conforming to IEC 947-3
2200 W AC-23A, 690 V 3 phases conforming to IEC 947-3
4800 W AC-21, 230 V 3 phases conforming to IEC 947-3
600 W AC-3, 230 V 1 phase conforming to IEC 947-3
8300 W AC-21, 400 V 3 phases conforming to IEC 947-3

[le] Rated Operational Current Ac	1.8 A at 690 V AC-3 3 phases conforming to IEC 947-3 2.8 A at 500 V AC-3 3 phases conforming to IEC 947-3 2.8 A at 690 V AC-23A 3 phases conforming to IEC 947-3 3.3 A at 400 V AC-3 3 phases conforming to IEC 947-3 3.8 A at 500 V AC-23A 3 phases conforming to IEC 947-3 4.6 A at 230 V AC-3 3 phases conforming to IEC 947-3 4.8 A at 400 V AC-23A 3 phases conforming to IEC 947-3 5.6 A at 230 V AC-23A 3 phases conforming to IEC 947-3 1 A at 500 V AC-15 conforming to IEC 947-5-1 2 A at 400 V AC-15 conforming to IEC 947-5-1 3 A at 230 V AC-15 conforming to IEC 947-5-1	
Electrical Durability	1000000 cycles AC-15 1000000 cycles AC-21 500000 cycles AC-23 500000 cycles AC-3	
Maximum Operating Rate	2.5 cyc/mn AC-21 2.5 cyc/mn AC-23 2.5 cyc/mn AC-3 8.333 cyc/mn AC-15	
Short-Circuit Current	10000 A	
Short-Circuit Protection	16 A cartridge fuse, type gG	
[Uimp] Rated Impulse Withstand Voltage	4 kV in isolating function 6 kV conforming to IEC 947-1	
Contact Operation	Slow-break	
Positive Opening	With	
Electrical Connection	Captive screw clamp terminals flexible, clamping capacity: 2 x 1.5 mm² Captive screw clamp terminals solid, clamping capacity: 1 x 2.5 mm²	
Mechanical Durability	1000000 cycles	
Cad Overall Width	45 mm	
Cad Overall Height	50 mm	
Cad Overall Depth	59 mm	
Net Weight	0.16 kg	
Environment		
Standards	IEC 60947-3 for power circuit IEC 60947-5-1 for control circuit CENELEC EN 50013	
Product Certifications	CSA 240 V 3 hp 3 phases 2 pole(s) UL 240 V 0.33 hp 1 phase 2 pole(s) CSA 240 V 1 hp 1 phase UL 240 V 1 hp 3 phases	
Protective Treatment	TC	
Ambient Air Temperature For Operation	-2555 °C	
Ambient Air Temperature For Storage	-4070 °C	
Shock Resistance	30 gn conforming to IEC 68-2-27	
Vibration Resistance	5 gn conforming to IEC 68-2-6 (f = 10150 Hz)	
Electrical Shock Protection Class	Class II conforming to IEC 536 Class II	
Packing Units		
Unit Type Of Package 1	PCE	

Number Of Units In Package 1

Package 1 Height

1

6.500 cm

Package 1 Width	6.500 cm
Package 1 Length	11.000 cm
Package 1 Weight	170.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.844 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	320
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	67.008 kg

# **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium"

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations


# **Product datasheet**

### K1D002UCH

**Dimensions Drawings** 

#### Operating Head and Body with Plastic Base

#### Front Mounting by Ø 22 mm/0.87 in. Hole



- a1 80.5 mm/3.17 in.
- e support panel thickness 1 mm to 6 mm./0.039 in. to 0.24 in.


### K1D002UCH

**Technical Description** 

#### **Link Positions (Factory Mounted)**

#### Diagram for 1 to 4-pole Switches

Select the number of poles according to the product characteristics.



# **Product datasheet**

# K1D002UCH

#### **Marking**



#### **Angular Position of Switch**




### K1D002UCH

#### **Switching Program**

#### Diagram for 1 to 4-pole Switches

Select the number of poles according to the product characteristics.



- (1) 1-pole
- (2) 2-pole
- (3) 3-pole
- (4) 4-pole

#### **Convention Used for Switching Program Representation**

Contact closed

Contact closed in 2 positions and maintained between the 2 positions

Sealed assembly for auto-maintain control

Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:

10

