Product datasheet

Specifications





Cam ammeter switch, Harmony K, multifixing, plastic,3 positions, position 0, 90°,12A, 45x45mm,metallic legend,marked 0 L1 L2 L3, 35mm black handle

K1F003MLH

Main

Range Of Product	Harmony K	
Product Or Component Type	Complete cam switch	
Component Name	K1	
[Ith] Conventional Free Air Thermal Current	12 A	
Product Mounting	Front mounting	
Fixing Mode	Multifixing	
Cam Switch Head Type	With front plate 45 x 45 mm	
Type Of Operator	Black handle, length = 35 mm	
Rotary Handle Padlocking	Without	
Presentation Of Legend	With metallic legend, 0 - L1 - L2 - L3 black marking	
Cam Switch Function	Ammeter switch	
Return	Without	
Type Of Measurement	For 3 circuits	
Off Position	With Off position	
Switching Positions	Right: 0° - 90° - 180° - 270°	
Ip Degree Of Protection	IP40 conforming to IEC 529 IP40 conforming to NF C 20-010	

Complementary

Switching Angle	90 °
[Ui] Rated Insulation Voltage	690 V (pollution degree 3) conforming to IEC 60947-1
[Ithe] Conventional Enclosed Thermal Current	10 A
Rated Operational Power In W	10500 W AC-21, 500660 V 3 phases conforming to IEC 60947-3 1100 W AC-3, 230 V 3 phases conforming to IEC 60947-3 1500 W AC-23A, 230 V 3 phases conforming to IEC 60947-3 1500 W AC-3, 400 V 1 phase conforming to IEC 60947-3 1500 W AC-3, 400 V 3 phases conforming to IEC 60947-3 1500 W AC-3, 500 V 3 phases conforming to IEC 60947-3

1500 W AC-3, 690 V 3 phases conforming to IEC 60947-3 2200 W AC-23A, 400 V 3 phases conforming to IEC 60947-3 2200 W AC-23A, 500 V 3 phases conforming to IEC 60947-3 2200 W AC-23A, 690 V 3 phases conforming to IEC 60947-3 4800 W AC-21, 230 V 3 phases conforming to IEC 60947-3 600 W AC-3, 230 V 1 phase conforming to IEC 60947-3 8300 W AC-21, 400 V 3 phases conforming to IEC 60947-3

[le] Rated Operational Current Ac	1 A at 500 V AC-15 conforming to IEC 60947-5-1 2 A at 400 V AC-15 conforming to IEC 60947-5-1 3 A at 230 V AC-15 conforming to IEC 60947-5-1 1.8 A at 690 V AC-3 3 phases conforming to IEC 60947-3 2.8 A at 500 V AC-3 3 phases conforming to IEC 60947-3 2.8 A at 690 V AC-23A 3 phases conforming to IEC 60947-3 3.3 A at 400 V AC-3 3 phases conforming to IEC 60947-3 3.8 A at 500 V AC-23A 3 phases conforming to IEC 60947-3 4.6 A at 230 V AC-3 3 phases conforming to IEC 60947-3 4.8 A at 400 V AC-23A 3 phases conforming to IEC 60947-3 5.6 A at 230 V AC-23A 3 phases conforming to IEC 60947-3	
Electrical Durability	1000000 cycles AC-15 1000000 cycles AC-21 500000 cycles AC-23 500000 cycles AC-3	
Maximum Operating Rate	2.5 cyc/mn AC-21 2.5 cyc/mn AC-23 2.5 cyc/mn AC-3 8.333 cyc/mn AC-15	
Short-Circuit Current	10000 A	
Short-Circuit Protection	16 A cartridge fuse, type gG	
[Uimp] Rated Impulse Withstand Voltage	4 kV in isolating function 6 kV conforming to IEC 60947-1	
Contact Operation	Slow-break	
Positive Opening	With	
Electrical Connection	Captive screw clamp terminals flexible, clamping capacity: 2 x 1.5 mm ² Captive screw clamp terminals solid, clamping capacity: 1 x 2.5 mm ²	
Mechanical Durability	1000000 cycles	
Cad Overall Width	45 mm	
Cad Overall Height	45 mm	
Cad Overall Depth	97 mm	
Net Weight	0.17 kg	
Environment		

Standards	CENELEC EN 50013 EN/IEC 60947-3 for power circuit EN/IEC 60947-5-1 for control circuit	
Product Certifications	CSA 240 V 1 hp 1 phase CSA 240 V 3 hp 3 phases 2 pole(s) UL 240 V 1 hp 3 phases UL 240 V 0.33 hp 1 phase 2 pole(s)	
Protective Treatment	TC	
Ambient Air Temperature For Operation	-2555 °C	
Ambient Air Temperature For Storage	-4070 °C	
Shock Resistance	30 gn conforming to IEC 68-2-27	
Vibration Resistance	5 gn conforming to IEC 68-2-6 (f = 10150 Hz)	
Electrical Shock Protection Class	Class II conforming to IEC 536 Class II conforming to NF C 20-030	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.600 cm

Package 1 Width	6.600 cm
Package 1 Length	11.200 cm
Package 1 Weight	180.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	40
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.655 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	320
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	70.820 kg

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations


Product datasheet

K1F003MLH

Dimensions Drawings

Operating Head and Body

Front Mounting "Multi-Fixing"




- a 73 mm/2.87 in.
- e support panel thickness 1 mm to 6 mm./0.039 in. to 0.24 in.

K1F003MLH

Technical Description

Link Positions (Factory Mounted)



Marking




Angular Position of Switch



Product datasheet

K1F003MLH

Switching Program



Convention Used for Switching Program Representation

Contact closed


Contact closed in 2 positions and maintained between the 2 positions

Sealed assembly for auto-maintain control

Overlapping contacts

Spring return position: for a switching angle of 90°, spring return is over 30° after the last position (for a maximum of 3 simultaneous contacts).

Example:



10