Product datasheet

Specification





Miniature circuit breaker (MCB), Multi9 C60H-DC, 1P, 16A, C curve, 5kA (UL 1077), 6kA (IEC/ EN 60947-2)

M9U21116

Main

Walli		
Range	Multi9	
Product Name	Multi9 C60H-DC	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	C60H-DC	
Device Application	Distribution	
Poles Description	1P	
Number Of Protected Poles	1	
[In] Rated Current	16 A at 25 °C conforming to EN/IEC 60947-2	
Network Type	DC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	С	
Breaking Capacity	10 kA Icu at 220 V DC conforming to EN/IEC 60947-2 6 kA Icu at 250 V DC conforming to EN/IEC 60947-2 20 kA Icu at 110 V DC conforming to EN/IEC 60947-2 5 kA AIR at 12250 V DC conforming to UL 1077 10 kA Icu at 220 V DC conforming to GB 14048.2 6 kA Icu at 250 V DC conforming to GB 14048.2 20 kA Icu at 110 V DC conforming to GB 14048.2	
Utilisation Category	Category A conforming to EN/IEC 60947-2	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	
Standards	EN/IEC 60947-2 GB 14048.2 UL 1077	
Product Certifications	IEC CCC UR	

Complementary

[Ue] Rated Operational Voltage	250 V DC 110 V DC 220 V DC	
Magnetic Tripping Limit	710 x ln DC	
[Ics] Rated Service Breaking Capacity	7.5 kA 75 % conforming to EN/IEC 60947-2 - 220 V DC 4.5 kA 75 % conforming to EN/IEC 60947-2 - 250 V DC 15 kA 75 % conforming to EN/IEC 60947-2 - 110 V DC 7.5 kA 75 % conforming to GB 14048.2 - 220 V DC 4.5 kA 75 % conforming to GB 14048.2 - 250 V DC 15 kA 75 % conforming to GB 14048.2 - 110 V DC	
[Ui] Rated Insulation Voltage	500 V DC conforming to EN/IEC 60947-2	

[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	73 mm
Net Weight	0.128 kg
Colour	Grey
Mechanical Durability	20000 cycles
Electrical Durability	3000 cycles 250 V DC L/R = 2 ms 6000 cycles 250 V DC
Provision For Padlocking	Padlockable
Connections - Terminals	Tunnel type terminal (top or bottom)125 mm² (AWG 18AWG 4) - rigid stranded Tunnel type terminal (top or bottom)116 mm² (AWG 18AWG 6) - flexible Tunnel type terminal (top or bottom)116 mm² (AWG 18AWG 6) - flexible with ferrule Tunnel type terminal (top or bottom) - 2 cable(s) 110 mm² (AWG 18AWG 8) - rigid stranded Tunnel type terminal (top or bottom) - 2 cable(s) 110 mm² (AWG 18AWG 8) - flexible Tunnel type terminal (top or bottom) - 2 cable(s) 110 mm² (AWG 18AWG 8) - flexible with ferrule Tunnel type terminal (top or bottom) - 3 cable(s) 1 mm² (AWG 18) - flexible stranded
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2.5 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Heat Dissipation	2.5 W at 220 V - 16 A
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-2 2 conforming to GB 14048.2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	7.2 cm

Package 1 Length	8.2 cm
Package 1 Weight	113.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.2 cm
Package 2 Width	9.0 cm
Package 2 Length	22.5 cm
Package 2 Weight	1.406 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	17.227 kg

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
	EU RONS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations