# **Product datasheet**

Specifications





Cam switch, Harmony K, multifixing, plastic, 4 poles, 2 positions, 90°, 20A, 45x45mm, metallic legend, marked 0 1, 35mm black handle

K2D004HLH

### Main

Range Of Product	Harmony K	
Product Or Component Type	Complete cam switch	
Component Name	K2	
[Ith] Conventional Free Air Thermal Current	20 A	
Mounting Location	Front	
Fixing Mode	Multifixing	
Cam Switch Head Type	With front plate 45 x 45 mm	
Type Of Operator	Black handle, length = 35 mm	
Rotary Handle Padlocking	Without	
Presentation Of Legend	With metallic legend, 0 - 1 black marking	
Cam Switch Function	Switch	
Return	Without	
Off Position	With Off position	
Poles Description	4P	
Switching Positions	Right: 0° - 90°	
Degree Of Protection IP40 conforming to IEC 60529		

## Complementary

Switching Angle	90 °	
[Ui] Rated Insulation Voltage	690 V (pollution degree 3) conforming to IEC 60947-1	
[Ithe] Conventional Enclosed Thermal Current	16 A	
Electrical Durability	200000 cycles AC-23 200000 cycles AC-3 600000 cycles AC-15 600000 cycles AC-21	
Maximum Operating Rate	2.5 cyc/mn AC-21 2.5 cyc/mn AC-23 2.5 cyc/mn AC-3 8.333 cyc/mn AC-15	
Short-Circuit Current	10000 A	
Short-Circuit Protection	on 20 A cartridge fuse, type gG	
[Uimp] Rated Impulse Withstand 4 kV in isolating function Voltage 6 kV conforming to IEC 60947-1		

Contact Operation	Slow-break	
Positive Opening	With	
Electrical Connection	Captive screw clamp terminals flexible, clamping capacity: 2 x 1.5 mm <sup>2</sup> Captive screw clamp terminals solid, clamping capacity: 1 x 2.5 mm <sup>2</sup>	
Mechanical Durability	1000000 cycles	
Cad Overall Width	45 mm	
Cad Overall Height	45 mm	
Cad Overall Depth	87 mm	
Net Weight	0.14 kg	

### **Environment**

Standards	IEC 60947-3 for power circuit IEC 60947-5-1 for control circuit CENELEC EN 50013 GB/T 14048.5 for control circuit GB/T 14048.3 for power circuit	
Product Certifications	CSA 240 V 3 hp 3 phases 2 -pole(s) UL 240 V 0.33 hp 1 phase 2 -pole(s) CSA 240 V 1 hp 1 phase UL 240 V 1 hp 3 phases CCC	
Protective Treatment	TC	
Ambient Air Temperature For Operation	-2555 °C	
Ambient Air Temperature For Storage	-4070 °C	
Shock Resistance	30 gn conforming to IEC 68-2-27	
Vibration Resistance	Resistance 5 gn conforming to IEC 68-2-6 (f = 10150 Hz)	
Overvoltage Category	Class II conforming to IEC 536 Class II conforming to NF C 20-030	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.6 cm
Package 1 Width	6.5 cm
Package 1 Length	11.0 cm
Package 1 Weight	164.0 g

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations